

PREMIUM, FDA APPROVED MATERIAL (*), REDUCES GLOVE CHANGES (**)

Port size: 305mm/12"

Thickness: 0.6mm/24 mil

- **Optimized durability:** The AlphaTec® EPDM Isolator Glove 85-505 is designed for repeated autoclave sterilization (up to 50 times), resulting in fewer replacements
- **Assured protection:** These isolator gloves satisfy EN ISO 374 chemical resistance standards, for assured protection from hydrogen peroxide and common disinfecting chemicals
- **Extended glove life:** They can bear sustained oxygen, UV ray and ozone exposure without rapid aging
- **Food handling compliance:** These EPDM gloves adhere to FDA Food Contact regulation 21 CFR 177 (FDA Positive List) for Indirect Food Additives



KEY FEATURES & BENEFITS

- **EPDM composition:** Suitable for repeated autoclave sterilization
- **Chemical resistance:** Hydrogen peroxide/common disinfecting chemicals
- **FDA food handling compliance:** For safe, dependable isolator gloves

TECHNICAL DATA SHEET

Product Reference	85-505
Material	Ethylene propylene diene rubber_EPDM
Color	Black
Shape	Ambidextrous
External Glove Surface	Smooth
Cuff Style	Beaded
Storage Instructions	Store in a dry and dark environment, temperature of 5°C to 22°C. Retain in original packaging when not in use.
Available Sizes	11, 9.5
Temperature Range	From -20°C to 130°C
Cleanroom Class	Non-Critical Environment
Shelf Life	Three (3) years from date of manufacture.
Tested For Use With Chemotherapy Drugs	No
Standards	CE 0493, EN 388:2016, EN ISO 21420:2020, EN ISO 374-1:2016 Type B, EN ISO 374-5:2016, Category III, UKCA
Vulcanization Chemical Accelerators	- Diphenyl guanidine - Tetramethylthiuram disulfide

PHYSICAL PROPERTIES

	Typical Values	Testing Method
Typical Length (mm/in)	800/32	EN ISO 21420
Port Size	305mm/12"	
Target Single Wall Palm Thickness (mm/mil)	0.60 / 24	EN 455-2
Target Single Wall Finger Thickness (mm/mil)	0.60 / 24	EN 455-2
Target Single Wall Cuff Thickness (mm/mil)	0.60 / 24	EN 455-2

PROTECTION AGAINST MECHANICAL RISKS, EN 388:2016+A1:2018

Risk	Performance level
Abrasion Resistance	Level 2
Blade Cut Resistance	Level 1
Tear Resistance	Level 1
Puncture Resistance	Level 1
ISO 13997 Cut Resistance	Level A

ORDERING INFORMATION

	PORT SIZE	12"/305mm	12"/305mm
	SIZE	9.5	11
85-505	REORDER NO.	85505095	85505110

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.