

RAFIX 16, blanking caps, black



description

Blanking plugs are used for installation in mounting holes in the front panel that are not required.

technical data

> general

Bezel color	black
Collar shape	square alignable in rows
Operating temperature, min.	-25 °C
Operating temperature, max.	70 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	80 °C
illuminated	No
Packaging unit	10 pcs.
net weight	4.6 g
Degree of protection, front side, according to DIN EN 60529	IP65
MOQ order	10 pcs.
RoHS compliant	Yes
REACH compliant	Yes

direct links

> RAFI eCatalog

> mounting diameters

Outside dimension, length	25 mm
Outside dimension, width	25 mm
Outside dimension, height	24.7 mm
Mounting hole	16.2 mm

> mechanical data

Fixing	Threaded ring
Threaded ring torque, max.	1.2 Nm

drawings

Dimensioned drawing

