

Pluggable hydraulic compression head SU210K

POWER 200 kN

- Crimping of non insulated terminals from 10 to 150 mm².
- Anti-corrosion coating (nickel).
- To be connected to 700 bars hydraulic pump or sets.
- Delivered with female semi-coupler p/n : RKF-M38NPT.
- Length: 260 mm.
- Weight: 5.8 Kg.

Accessories

Die holder **S21**

Ref.
SU210K



Pluggable hydraulic compression head VF210K with closed head

POWER 200 kN

- Crimping of non insulated terminals from 10 to 150 mm².
- Anti-corrosion coating (nickel).
- To be connected to 700 bars hydraulic pump or sets.
- Delivered with female semi-coupler p/n : RKF-M38NPT.
- Length: 275 mm.
- Weight: 6.2 Kg.

Accessories

Die holder **S21**

Ref.
VF210K



Crimping dies:

Dies	Cross section (mm ²)	Terminals series	Dies p/n SU210K/ VF210K + S21 die holder	Cross section (mm ²)	Terminals series	Dies p/n SU210K/ VF210K + S21 die holder	Cross section (mm ²)	Terminals series	Dies p/n SU210K/ VF210K + S21 die holder																																																																																																																																																																																																																						
<table border="1"> <tr> <td colspan="3">ELS/FLS series</td> <td colspan="3">TRS serie</td> <td colspan="4">AL serie</td> </tr> <tr> <td>10</td> <td>ELS</td> <td>ELSV20</td> <td>95</td> <td>TRS95</td> <td>TRS95V20</td> <td>50</td> <td>AL50</td> <td>AL50V20</td> </tr> <tr> <td>16</td> <td>FLS</td> <td>FLSV20</td> <td>120</td> <td>TRS446</td> <td>TRS446V20</td> <td>60</td> <td>AL60</td> <td>AL60V20</td> </tr> <tr> <td colspan="3">TN serie</td> <td>120</td> <td>TRS448</td> <td>TRS448V20</td> <td>70</td> <td>AL70</td> <td>AL70V20</td> </tr> <tr> <td>25</td> <td>TN25</td> <td>TN25V20</td> <td>150</td> <td>TRS450</td> <td>TRS450V20</td> <td>95</td> <td>AL95</td> <td>AL95V20</td> </tr> <tr> <td>35</td> <td>TN35</td> <td>TN35V20</td> <td>185</td> <td>TRS452</td> <td>TRS452V20</td> <td>120</td> <td>AL120</td> <td>AL120V20</td> </tr> <tr> <td>50</td> <td>TN50</td> <td>TN50V20</td> <td>240</td> <td>TRS455</td> <td>TRS455V20</td> <td>150</td> <td>AL150 - AL150B</td> <td>AL150V20</td> </tr> <tr> <td>70</td> <td>TN70</td> <td>TN70V20</td> <td>240</td> <td>TRS453</td> <td>TRS453V20</td> <td>185</td> <td>AL185</td> <td>AL185V20</td> </tr> <tr> <td>95</td> <td>TN95</td> <td>TN95V20</td> <td>400</td> <td>TRS456</td> <td>TRS456V20</td> <td>240</td> <td>AL240</td> <td>AL240V20</td> </tr> <tr> <td>120</td> <td>TN120</td> <td>TN120V20</td> <td>185</td> <td>TRS185 - TRS185-1B</td> <td>TRS185V20</td> <td>300</td> <td>AL300</td> <td>AL300V20</td> </tr> <tr> <td>150</td> <td>TN150</td> <td>TN150V20</td> <td>240</td> <td>TRS240 - TRS240-1B</td> <td>TRS240V20</td> <td>460</td> <td>AL460</td> <td>AL460V20</td> </tr> <tr> <td>185</td> <td>TN185</td> <td>TN185V20</td> <td>240</td> <td>TRS242-12</td> <td>TRS258V20</td> <td></td> <td></td> <td></td> </tr> <tr> <td>240</td> <td>TN240</td> <td>TN240V20</td> <td>240</td> <td>TRS400</td> <td>TRS400V20</td> <td></td> <td></td> <td></td> </tr> <tr> <td>300</td> <td>TN300</td> <td>TN300V20</td> <td>400</td> <td>TRS400</td> <td>TRS400V20</td> <td></td> <td></td> <td></td> </tr> <tr> <td colspan="3">TR serie</td> <td>95</td> <td>TRS262</td> <td>TRS262V20S (sertissage sur âme)</td> <td></td> <td></td> <td></td> </tr> <tr> <td>95</td> <td>TR95</td> <td>TR95V20</td> <td>120</td> <td>TR120</td> <td>TR120V20</td> <td></td> <td></td> <td></td> </tr> <tr> <td>150</td> <td>TR150</td> <td>TR150V20</td> <td>185</td> <td>TR185</td> <td>TR185V20</td> <td></td> <td></td> <td></td> </tr> <tr> <td>240</td> <td>TR240</td> <td>TR240V20</td> <td>240</td> <td>TR240</td> <td>TR240V20</td> <td></td> <td></td> <td></td> </tr> <tr> <td>300</td> <td>TR300</td> <td>TR300V20</td> <td>300</td> <td>TR300</td> <td>TR300V20</td> <td></td> <td></td> <td></td> </tr> <tr> <td>400</td> <td>TR400</td> <td>TR400V20</td> <td>400</td> <td>TR400</td> <td>TR400V20</td> <td></td> <td></td> <td></td> </tr> <tr> <td>500</td> <td>TR500</td> <td>TR500V20</td> <td>500</td> <td>TR500</td> <td>TR500V20</td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td>50</td> <td>TRS262</td> <td>TRS262V20F (sertissage sur isolant)</td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td>95</td> <td>TRS246</td> <td>TRS246V20S</td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> <td>TRS246V20F</td> <td></td> <td></td> <td></td> </tr> </table>							ELS/FLS series			TRS serie			AL serie				10	ELS	ELSV20	95	TRS95	TRS95V20	50	AL50	AL50V20	16	FLS	FLSV20	120	TRS446	TRS446V20	60	AL60	AL60V20	TN serie			120	TRS448	TRS448V20	70	AL70	AL70V20	25	TN25	TN25V20	150	TRS450	TRS450V20	95	AL95	AL95V20	35	TN35	TN35V20	185	TRS452	TRS452V20	120	AL120	AL120V20	50	TN50	TN50V20	240	TRS455	TRS455V20	150	AL150 - AL150B	AL150V20	70	TN70	TN70V20	240	TRS453	TRS453V20	185	AL185	AL185V20	95	TN95	TN95V20	400	TRS456	TRS456V20	240	AL240	AL240V20	120	TN120	TN120V20	185	TRS185 - TRS185-1B	TRS185V20	300	AL300	AL300V20	150	TN150	TN150V20	240	TRS240 - TRS240-1B	TRS240V20	460	AL460	AL460V20	185	TN185	TN185V20	240	TRS242-12	TRS258V20				240	TN240	TN240V20	240	TRS400	TRS400V20				300	TN300	TN300V20	400	TRS400	TRS400V20				TR serie			95	TRS262	TRS262V20S (sertissage sur âme)				95	TR95	TR95V20	120	TR120	TR120V20				150	TR150	TR150V20	185	TR185	TR185V20				240	TR240	TR240V20	240	TR240	TR240V20				300	TR300	TR300V20	300	TR300	TR300V20				400	TR400	TR400V20	400	TR400	TR400V20				500	TR500	TR500V20	500	TR500	TR500V20							50	TRS262	TRS262V20F (sertissage sur isolant)							95	TRS246	TRS246V20S									TRS246V20F			
ELS/FLS series			TRS serie			AL serie																																																																																																																																																																																																																									
10	ELS	ELSV20	95	TRS95	TRS95V20	50	AL50	AL50V20																																																																																																																																																																																																																							
16	FLS	FLSV20	120	TRS446	TRS446V20	60	AL60	AL60V20																																																																																																																																																																																																																							
TN serie			120	TRS448	TRS448V20	70	AL70	AL70V20																																																																																																																																																																																																																							
25	TN25	TN25V20	150	TRS450	TRS450V20	95	AL95	AL95V20																																																																																																																																																																																																																							
35	TN35	TN35V20	185	TRS452	TRS452V20	120	AL120	AL120V20																																																																																																																																																																																																																							
50	TN50	TN50V20	240	TRS455	TRS455V20	150	AL150 - AL150B	AL150V20																																																																																																																																																																																																																							
70	TN70	TN70V20	240	TRS453	TRS453V20	185	AL185	AL185V20																																																																																																																																																																																																																							
95	TN95	TN95V20	400	TRS456	TRS456V20	240	AL240	AL240V20																																																																																																																																																																																																																							
120	TN120	TN120V20	185	TRS185 - TRS185-1B	TRS185V20	300	AL300	AL300V20																																																																																																																																																																																																																							
150	TN150	TN150V20	240	TRS240 - TRS240-1B	TRS240V20	460	AL460	AL460V20																																																																																																																																																																																																																							
185	TN185	TN185V20	240	TRS242-12	TRS258V20																																																																																																																																																																																																																										
240	TN240	TN240V20	240	TRS400	TRS400V20																																																																																																																																																																																																																										
300	TN300	TN300V20	400	TRS400	TRS400V20																																																																																																																																																																																																																										
TR serie			95	TRS262	TRS262V20S (sertissage sur âme)																																																																																																																																																																																																																										
95	TR95	TR95V20	120	TR120	TR120V20																																																																																																																																																																																																																										
150	TR150	TR150V20	185	TR185	TR185V20																																																																																																																																																																																																																										
240	TR240	TR240V20	240	TR240	TR240V20																																																																																																																																																																																																																										
300	TR300	TR300V20	300	TR300	TR300V20																																																																																																																																																																																																																										
400	TR400	TR400V20	400	TR400	TR400V20																																																																																																																																																																																																																										
500	TR500	TR500V20	500	TR500	TR500V20																																																																																																																																																																																																																										
			50	TRS262	TRS262V20F (sertissage sur isolant)																																																																																																																																																																																																																										
			95	TRS246	TRS246V20S																																																																																																																																																																																																																										
					TRS246V20F																																																																																																																																																																																																																										

