

Combi Drill LXT®

DHP484

18V • 54 Nm • 0 – 2 000 min⁻¹

A powerful, brushless general-use impact drill for screwdriving and drilling

An efficient, brushless drill for professional screwdriving and drilling with or without hammer action, two power settings. Max. torque of 54 / 30 Nm. A versatile tool for fitters, builders and maintenance staff. Integrated LED light.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 500 / 2000 min ⁻¹
Max. fastening torque Hard/Soft	54 / 30 Nm
Max Torque	65 Nm
Torque setting	21
Impacts per Minute (IPM)	0 - 7500 / 30000 min ⁻¹
Max. Drilling Diameter in Masonry	13 mm
Max. Drilling Diameter in Concrete	13 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	38 mm
Drilling Capacity Flat bit	38 mm
Drilling Capacity Hole Saw	51 mm

User benefits

- Brushless maintenance-free and long-life motor
- With impact mode, the tool can be used for drilling stone materials.
- Ergonomic soft grip handle provides increased comfort
- LED light illuminates the work site
- Electronic overload protection protects the user and the device
- All metal gear construction ensures high transmission durability
- Mechanical 2-speed gearing; High speed mode for speedy drilling in light duty applications; Low speed mode for heavy duty applications requiring high torque
- Electric brake for maximum productivity and increased operator safety
- Reversing switch is conveniently located
- Highly efficient and compact machine for professional use
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Optional AC

784637-8

Screw Bit, Ph2 – S6, 45 Mm, Double

837916-4

MakPac (2) Inlay

D-42204

COUNTERSINK 6PC SET

E-07076

Screw bit set 32 pcs



821550-0

Makpac case (2)



B-49432

Drill Bit Set, TCT, M-Force, 18 pcs



D-47363

Forstner Drill Bit Set, 5 pcs



E-08698

Flat bit set 8 pcs



Other

User manual

Parts drawing