

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [98266-0215](#)
Status: **Active**
Overview: Premo-Flex™ FFC and Etched Polyimide Jumpers
Description: 0.50mm Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 20 Circuits, 0.152m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-98266-001 \(PDF\)](#)
[Product Specification PS-98266-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	98266
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	<u>Premo-Flex™ FFC and Etched Polyimide Jumpers</u>
Product Name	Premo-Flex™ FFC Jumper
UPC	756054771624

Physical

Cable Length	0.152m
Circuits (Loaded)	20
Net Weight	0.990/g
Packaging Type	Bag
Pitch - Termination Interface	0.50mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-98266-001
Product Specification	PS-98266-001
Sales Drawing	SD-98266-001



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[98266Series](#)

Use With

www.molex.com/link/ffc-fpc.html>Molex FFC – FPC connector. Be sure to match like plating

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION