

FEATURES

- **Magnetic Cylindrical Sensor:** Ensures accurate detection and switching action
- **Cable 2 Wire Connection:** Simplifies installation and maintenance
- **IP67 Rating:** Offers excellent protection against dust and water ingress
- **LED Indicator:** Provides clear visual status indication
- **Wide Voltage Range (5 – 240 V AC/DC):** Compatible with various power supplies
- **Reed Switch Output Function:** Delivers reliable switching performance
- **Compact Dimensions (33 mm x 5 mm x 5 mm):** Allows for easy integration into tight spaces
- **Operating Temperature Range (-10°C to 70°C):** Suitable for diverse environmental conditions

RS PRO Magnetic Switch, Cable 2 Wire, IP67

RS Stock No: 727-224



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Magnetic Switch is designed for reliable and efficient operation in industrial environments. It is primarily used with cylinders, providing precise control and feedback. Its robust construction and IP67 rating ensure durability and resistance to harsh conditions.

General Specifications

Electrical Connection Type	Cable 2 Wire
For Use With	Cylinder
LED Indicator	Yes
Measurement Principle	Magnetic Cylindrical Sensor
Output Function	Reed Switch
Product Type	Magnetic Switch

Mechanical Specifications

Depth	33 mm
Height	5 mm
Width	5 mm

Protection Category

IP Rating	IP67
-----------	------

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-10 °C

Approvals

Standards/Approvals	IEC 60529
---------------------	-----------

Electrical Specifications

Switching Action	NO
Voltage	5-240 V ac/dc