



The DNA of tech.™

Additional Strip Plating Line for SMC Commercial Grade TVS and Rectifier

For further information, please contact your regional Vishay office.

CONTACT INFORMATION

Americas

Vishay Semiconductors
One Greenwich Place
-
Shelton CT United States 06484
Phone: +1-402-563-6866
Fax: +1-402-563-6296
Diodes-Americas@vishay.com

Europe

Vishay Semiconductors
Theresienstrasse 2
-
Heilbronn Germany D-74072
Phone: +49 7131 7498 656 (715)
Fax: +49 7131 67 2938
Diodes-Europe@vishay.com

Asia

Vishay Semiconductors
37A Tampines Street 92 #07-01
-
Singapore 528886
Phone: +65 6788 6668
Fax: +65 6788 988
Diodes-Asia@vishay.com

Description of Change: In addition to the existing Barrel Plating, Vishay Diodes Division is introducing additional Strip Plating for Commercial grade TVS and Rectifier in SMC (DO-214AB) manufactured in Tianjin, China. There is no change in form, fit and function of the final products on customer application.

Upon the approval of this PCN, all future and customized part number for related product in the same package will adopt the same change.

Reason for Change: Capacity expansion

Expected Influence on Quality/Reliability/Performance: No change in quality and reliability performance

Part Numbers/Series/Families Affected: Please see materials list on the succeeding page.

Vishay Brand(S): Vishay General Semiconductor

Time Schedule:

Start Shipment Date: Monday June 8, 2026

Sample Availability: Available upon request

Product Identification: Plating traceability is done through Lot Number

Qualification Data: Available upon request

This PCN is considered approved, without further notification, unless we receive specific customer concerns before Wednesday June 3, 2026 or as specified by contract.

Issued By: Ivan Chen, Jill Li



Product Change Notification



Product Group: DD/Friday April 3, 2026/PCN-DD-007-2026-REV-0

The DNA of tech.™

3.0C100CA-M3/H	3.0C100CA-M3/I	3.0C10CA-M3/H	3.0C10CA-M3/I	3.0C110CA-M3/H
3.0C110CA-M3/I	3.0C120CA-M3/H	3.0C120CA-M3/I	3.0C12CA-M3/H	3.0C12CA-M3/I
3.0C13CA-M3/H	3.0C13CA-M3/I	3.0C14CA-M3/H	3.0C14CA-M3/I	3.0C15CA-M3/H
3.0C15CA-M3/I	3.0C16CA-M3/H	3.0C16CA-M3/I	3.0C17CA-M3/H	3.0C17CA-M3/I
3.0C18CA-M3/H	3.0C18CA-M3/I	3.0C20CA-M3/H	3.0C20CA-M3/I	3.0C22CA-M3/H
3.0C22CA-M3/I	3.0C24CA-M3/H	3.0C24CA-M3/I	3.0C26CA-M3/H	3.0C26CA-M3/I
3.0C28CA-M3/H	3.0C28CA-M3/I	3.0C28CA-M3C/I	3.0C30CA-M3/H	3.0C30CA-M3/I
3.0C33CA-M3/H	3.0C33CA-M3/I	3.0C36CA-M3/H	3.0C36CA-M3/I	3.0C40CA-M3/H
3.0C40CA-M3/I	3.0C43CA-M3/H	3.0C43CA-M3/I	3.0C45CA-M3/H	3.0C45CA-M3/I
3.0C48CA-M3/H	3.0C48CA-M3/I	3.0C51CA-M3/H	3.0C51CA-M3/I	3.0C54CA-M3/H
3.0C54CA-M3/I	3.0C58CA-01M3/H	3.0C58CA-M3/H	3.0C58CA-M3/I	3.0C58CA-M3C/I
3.0C60CA-M3/H	3.0C60CA-M3/I	3.0C64CA-M3/H	3.0C64CA-M3/I	3.0C64CA-M3C/I
3.0C70CA-M3/H	3.0C70CA-M3/I	3.0C70CA-M3C/I	3.0C75CA-01M3/H	3.0C75CA-M3/H
3.0C75CA-M3/I	3.0C78CA-M3/H	3.0C78CA-M3/I	3.0C85CA-01M3/H	3.0C85CA-M3/H
3.0C85CA-M3/I	3.0C90CA-01M3/H	3.0C90CA-M3/H	3.0C90CA-M3/I	S10CG-M3/I
S10CJ-M3/I	S10CK-M3/I	S10CM-M3/I	S10CQ-M3/I	S12CG-M3/I
S12CJ-M3/I	S12CK-M3/I	S12CM-M3/I	S12CQ-M3/I	S8CG-M3/I
S8CJ-M3/I	S8CJ-M3P/H	S8CK-M3/I	S8CM-M3/I	S8CM-M3P/H
S8CQ-M3/I	SMC3K22CA-M3/57	SMC3K22CA-M3/9A	SMC3K24CA-M3/57	SMC3K24CA-M3/9A
SMC3K26CA-M3/57	SMC3K26CA-M3/9A	SMC3K28CA-M3/57	SMC3K28CA-M3/9A	SMC3K30CA-M3/57
SMC3K30CA-M3/9A	SMC3K33CA-M3/57	SMC3K33CA-M3/9A	SMC3K36CA-M3/57	SMC3K36CA-M3/9A
SMC3K40CA-M3/57	SMC3K40CA-M3/9A	SMC3K43CA-M3/57	SMC3K43CA-M3/9A	SMC3K45CA-M3/57
SMC3K45CA-M3/9A	SMC3K48CA-M3/57	SMC3K48CA-M3/9A	SMC3K51CA-M3/57	SMC3K51CA-M3/9A
SMC3K54CA-M3/57	SMC3K54CA-M3/9A	SMC3K58CA-M3/57	SMC3K58CA-M3/9A	SMC3K60CA-M3/57
SMC3K60CA-M3/9A	SMC3K64CA-M3/57	SMC3K64CA-M3/9A	SMC3K70CA-M3/57	SMC3K70CA-M3/9A
SMC3K75CA-M3/57	SMC3K75CA-M3/9A	SMC3K78CA-M3/57	SMC3K78CA-M3/9A	SMC5K10A-M3/H
SMC5K10A-M3/I	SMC5K10CA-M3/H	SMC5K10CA-M3/I	SMC5K12A-M3/H	SMC5K12A-M3/I
SMC5K12CA-M3/H	SMC5K12CA-M3/I	SMC5K13A-M3/H	SMC5K13A-M3/I	SMC5K13A-M3C/H
SMC5K13CA-M3/H	SMC5K13CA-M3/I	SMC5K14A-M3/H	SMC5K14A-M3/I	SMC5K14A-M3C/H
SMC5K14CA-M3/H	SMC5K14CA-M3/I	SMC5K15A-M3/H	SMC5K15A-M3/I	SMC5K15A-M3C/H
SMC5K15CA-M3/H	SMC5K15CA-M3/I	SMC5K16A-M3/H	SMC5K16A-M3/I	SMC5K16CA-M3/H
SMC5K16CA-M3/I	SMC5K17A-M3/H	SMC5K17A-M3/I	SMC5K17CA-M3/H	SMC5K17CA-M3/I
SMC5K18A-M3/H	SMC5K18A-M3/I	SMC5K18CA-M3/H	SMC5K18CA-M3/I	SMC5K20A-M3/H
SMC5K20A-M3/I	SMC5K20CA-M3/H	SMC5K20CA-M3/I	SMC5K22A-M3/H	SMC5K22A-M3/I
SMC5K22CA-M3/H	SMC5K22CA-M3/I	SMC5K24A-M3/H	SMC5K24A-M3/I	SMC5K24CA-M3/H
SMC5K24CA-M3/I	SMC5K26A-M3/H	SMC5K26A-M3/I	SMC5K26CA-M3/H	SMC5K26CA-M3/I
SMC5K28A-M3/H	SMC5K28A-M3/I	SMC5K28CA-M3/H	SMC5K28CA-M3/I	SMC5K30A-M3/H
SMC5K30A-M3/I	SMC5K30CA-M3/H	SMC5K30CA-M3/I	SMC5K33A-M3/H	SMC5K33A-M3/I
SMC5K33CA-M3/H	SMC5K33CA-M3/I	SMC5K36A-M3/H	SMC5K36A-M3/I	SMC5K36CA-M3/H
SMC5K36CA-M3/I	SMC5K40A-M3/H	SMC5K40A-M3/I	SMC5K40CA-M3/H	SMC5K40CA-M3/I
SMC5K43A-M3/H	SMC5K43A-M3/I	SMC5K43CA-M3/H	SMC5K43CA-M3/I	SMC5K45A-M3/H
SMC5K45A-M3/I	SMC5K45CA-M3/H	SMC5K45CA-M3/I	SMC5K48A-M3/H	SMC5K48A-M3/I
SMC5K48CA-M3/H	SMC5K48CA-M3/I	SMC5K51A-M3/H	SMC5K51A-M3/I	SMC5K51CA-M3/H
SMC5K51CA-M3/I	SMC5K54A-M3/H	SMC5K54A-M3/I	SMC5K54A-M3C/I	SMC5K54CA-M3/H
SMC5K54CA-M3/I	SMC5K58A-M3/H	SMC5K58A-M3/I	SMC5K58A-M3C/H	SMC5K58CA-M3/H
SMC5K58CA-M3/I	SMC5K60A-01M3/H	SMC5K60A-01M3/I	SMC5K60A-M3/H	SMC5K60A-M3/I
SMC5K60CA-M3/H	SMC5K60CA-M3/I	SMC5K64A-M3/H	SMC5K64A-M3/I	SMC5K64CA-M3/H
SMC5K64CA-M3/I	SMC5K70A-M3/H	SMC5K70A-M3/I	SMC5K70CA-M3/H	SMC5K70CA-M3/I
SMC5K75A-M3/H	SMC5K75A-M3/I	SMC5K75CA-M3/H	SMC5K75CA-M3/I	SMC5K78A-M3/H
SMC5K78A-M3/I	SMC5K78CA-M3/H	SMC5K78CA-M3/I	SMC5K85A-M3/H	SMC5K85A-M3/I
SMC5K85CA-M3/H	SMC5K85CA-M3/I	XMC7K24CA-M3/H	XMC7K24CA-M3/I	