

TOLERANCE UNLESS OTHERWISE SPECIFIED .X ±0.25 .XX ±0.13

.XXX ±0.05

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER ORIGINAL


NYLON9T, UL94V-0

NOTES:

CURRENT RATING: 2A AC/DC **VOLTAGE RATING:** 100V AC/DC **TEMPERATURE RATING:** -25°C ~ 85°C **CONTACT RESISTANCE:** $10m\Omega$ MAX. **HOUSING RESISTANCE:** $1000M\Omega$ min. WITHSTANDING VOLTAGE: 800V AC / 60s

HOUSING MATERIAL: SOLDER TEMPERATURE

RESISTANCE: 250°C for 10s MAX



140 SERIES RIGHT ANGLE SMT MOUNT



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

| ACAD REFERENCE NO.: 140 A | ssembly |
|---------------------------|----------------------|
| DRAWN: C.B | DATE: March 28, 2020 |
| CHECKED: | DATE: |
| SCALE: 5:1 | SHEET 1 OF 1 |
| | |

DRAWING NUMBER: 140 Assembly **ISSUE** PART NUMBER: 140-504-417-060