

1-42-311

TRAPEZOIDAL LEVEL MLH 30CM

3253561423116



Product Description:

Solid aluminum alloy body - Larger horizontal vial for better visibility - Accuracy: 0.5 mm/m and machined sole



Product features and benefits:

- Even more accurate: 0.05 mm/m
- Milled soleplate Extra-large horizontal vial allows for faster and more accurate reading
- Its solid alloy body
- aluminum gives durability
- Its trapezoidal shape makes it easier to catch with a
- Improved ergonomics Rare earth magnets (MALH) for excellent hold

Product Warranty:

This product is covered by the legal warranty

Norms and standards applicable to the product:

- DIN 877

1-42-311

TRAPEZOIDAL LEVEL MLH 30CM

3253561423116



Part of the 1-42-311 series

Ref	▲ ▼ Title	▲ ▼
1-42-311	TRAPEZOIDAL LEVEL MLH 30CM	
1-42-312	TRAPEZOIDAL LEVEL MLH 40CM	
1-42-313	TRAPEZOIDAL LEVEL MLH 50CM	
1-42-314	TRAPEZOIDAL LEVEL MLH 60CM	
1-42-315	TRAPEZOIDAL LEVEL MLH 80CM	
1-42-316	TRAPEZOIDAL LEVEL MLH 100CM	