

PRODUCT-DETAILS

A50-30-11 230-240V 50Hz / 240-260V 60Hz A50-30-11 230-240V 50Hz / 240-260V 60Hz Contactor



General Information

Extended Product Type	A50-30-11 230-240V 50Hz / 240-260V 60Hz
Product ID	1SBL351001R8811
EAN	3471522082886
Catalog Description	A50-30-11 230-240V 50Hz / 240-260V 60Hz Contactor
Long Description	A50 contactors are mainly used for controlling 3-phase motors and generally for controlling power circuits up to 690 V AC / 1000 V AC or 220 V DC. The contactors can also be used for many other applications such as isolation, capacitor switching, lighting. The A... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles and 2 built-in auxiliary contacts, front and side-mounted add-on auxiliary contact blocks - Control circuit: AC operated with laminated magnet circuit - Accessories: a wide range of accessories is available.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Popular Downloads

Data Sheet, Technical Information	1SBC100122C0202_Ch02
Instructions and Manuals	FPTC407700P0003

Dimensions

Product Net Width	82 mm
Product Net Depth / Length	108 mm
Product Net Height	110 mm
Product Net Weight	1.2 kg

Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Auxiliary Contacts NC	1
Standards	Devices complying with international standards IEC 947-1 / 947-4-1, and European standards EN 60 947-1 / 60 947-4-1. Electromagnetic compatibility (EMC) acc. to amendment A11 to IEC 947-1, EN 60 947-1 and amendment 2 to IEC 947-4-1
Rated Operational Voltage	Main Circuit 1000 V
Rated Frequency (f)	Supply Circuit 50 60 Hz
Conventional Free-air Thermal Current (I _{th})	acc. to IEC 60947-4-1, Open Contactors q = 40 °C 100 A acc. to IEC 60947-5-1, q = 40 °C 16 A
Rated Operational Current AC-1 (I _e)	(690 V) 40 °C 100 (690 V) 55 °C 85 (690 V) 70 °C 70
Rated Operational Current AC-3 (I _e)	(415 V) 55 °C 50 A (440 V) 55 °C 45 A (500 V) 55 °C 45 A (690 V) 55 °C 35 A (1000 V) 55 °C 23 A (380 / 400 V) 55 °C 50 A (220 / 230 / 240 V) 55 °C 53
Rated Operational Power AC-3 (P _e)	(415 V) 25 kW (440 V) 25 kW (500 V) 30 kW (690 V) 30 kW (380 / 400 V) 22 kW (220 / 230 / 240 V) 15 kW
Rated Operational Power AC-6b (P _e)	(230 / 240 V) 40 °C, 50 / 60 Hz 22 kvar (230 / 240 V) 55 °C, 50 / 60 Hz 22 kvar (230 / 240 V) 70 °C, 50 / 60 Hz 20 kvar (400 / 415 V) 40 °C, 50 / 60 Hz 38 kvar (400 / 415 V) 70 °C, 50 / 60 Hz 34 kvar (400 / 415 V) 55 °C, 50 / 60 Hz 38 kvar (440 V) 40 °C, 50 / 60 Hz 42 kvar (440 V) 55 °C, 50 / 60 Hz 42 kvar (440 V) 70 °C, 50 / 60 Hz 37 kvar (500 / 550 V), 40 °C, 50 / 60 Hz 48 kvar (500 / 550 V) 55 °C, 50 / 60 Hz 48 kvar (500 / 550 V) 70 °C, 50 / 60 Hz 42 kvar (690 V) 40 °C, 50 / 60 Hz 65 kvar (690 V) 55 °C, 50 / 60 Hz 65 kvar (690 V) 70 °C, 50 / 60 Hz 58.5 kvar
Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1	8 x I _e AC-3
Rated Making Capacity AC-3 acc. to IEC 60947-4-1	10 x I _e AC-3
Rated Operational Current AC-15 (I _e)	(500 V) 2 A (690 V) 2 A (24 / 127 V) 6 A (220 / 240 V) 4 A

	(380 / 400 V) 3 A
Short-Circuit Protective Devices	Auxiliary Circuit - gG Type Fuses 10 A gG Type Fuses 100 A
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for I _e > 100 A) at 440 V 1300 A cos phi=0.45 (cos phi=0.35 for I _e > 100 A) at 690 V 630 A
Maximum Electrical Switching Frequency	(AC-1) 600 cycles per hour (AC-2 / AC-4) 150 cycles per hour (AC-3) 600 cycles per hour
Rated Operational Current DC-13 (I _e)	(24 V) 6 / 144 A (48 V) 2.8 / 134 A (72 V) 1 / 72 A (125 V) 0.55 / 69 A (250 V) 0.3 / 75 A
Rated Insulation Voltage (U _i)	acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V acc. to UL/CSA 600 V
Rated Impulse Withstand Voltage (U _{imp})	8 kV
Mechanical Durability	10 million
Maximum Mechanical Switching Frequency	3600 cycles per hour
Rated Control Circuit Voltage (U _c)	50 Hz 230 ... 240 V 60 Hz 240 ... 260 V
Coil Consumption	Average Holding Value 50 / 60 Hz 18 5.5 V-A Average Pull-in Value 50 Hz 190 V-A Average Pull-in Value 60 Hz 180 V-A
Operate Time	Between Coil De-energization and NC Contact Closing 7 ... 14 ms Between Coil De-energization and NO Contact Opening 4 ... 11 ms Between Coil Energization and NC Contact Opening 7 ... 22 ms Between Coil Energization and NO Contact Closing 8 ... 27 ms
Connecting Capacity Main Circuit	Flexible with Cable End 6 ... 16 mm ² Rigid Cable 6 ... 25 mm ²
Connecting Capacity Auxiliary Circuit	Flexible with Cable End 0.75 ... 2.5 mm ² Rigid Cable 1 ... 4 mm ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20
Connecting Terminals (delivered in open position) Main Poles	M 6 (+,-) pozidriv 2 screws with 1x (13 x 10 mm) connector
Terminal Type	Screw Terminals

Environmental

Ambient Air Temperature	Close to Contactor Fitted with Thermal O/L Relay -25 ... +55 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 U _c) -40 ... +55 °C Close to Contactor without Thermal O/L Relay (U _c) -40 ... +70 °C Close to Contactor for Storage -60 ... +80 °C
Climatic Withstand	acc. to IEC 60068-2-30 and 60068-2-11 - UTE C 63-100 specification II
Maximum Operating Altitude Permissible	3000 m
RoHS Status	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

ASEFA Certificate	ASEFA_10801-10901
BV Certificate	BV_2634H07559E0
CB Certificate	CB_CN45324
CCC Certificate	CCC_2018010304129267 CCC_2008010309289461
CQC Certificate	CQC2018010304129267 CQC2008010309289461
CSA Certificate	CSA_1033838_LR056745
Declaration of Conformity - CCC	2020980304001622 2020980304001226

Declaration of Conformity - CE	1SBD250801U1000
DNV Certificate	DNV-GL_TAE00000TX
DNV GL Certificate	DNV-GL_TAE00000TX
EAC Certificate	EAC_RU C-FR ME77 B03599
Environmental Information	1SBD250008E1003
Instructions and Manuals	FPTC407700P0003
LOVAG Certificate	LOVAG_FR01001
LR Certificate	LRS_9830011E4
RINA Certificate	RINA_ELE172319XG001
RMRS Certificate	RMRS_0507015250
RoHS Information	1SBD250801U1000
UL Certificate	UL_20120830-E312527-10-1
UL Listing Card	UL_E312527

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	140 mm
Package Level 1 Depth / Length	146 mm
Package Level 1 Height	96 mm
Package Level 1 Gross Weight	1.2 kg
Package Level 1 EAN	3471522082886
Package Level 2 Units	box 20 piece
Package Level 2 Width	503 mm
Package Level 2 Depth / Length	153 mm
Package Level 2 Height	307 mm
Package Level 2 Gross Weight	24 kg
Package Level 3 Units	160 piece

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
eClass	V11.0 : 27371003
UNSPSC	39121529

Where Used (as a spare part for "Products")

Identifier	Description	Quantity	Unit Of Measure
FC-0460-0040	No Description Available	1	piece

Product specific part data		
Product	Category	Drive Part Category
FC-0460-0040	MoCon	Switches, Relays, Contactors

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors
Drives → Low voltage AC drives → Legacy AC drives → MoCon

