



Oil



Light Duty

Liquid-repellent gloves offering advanced durability, comfort and dexterity

- **Specialized protection:** HyFlex® 11-919 light-duty industrial gloves are fully coated in nitrile, providing comprehensive protection from liquid, oil, grease and dirt
- **Improved durability:** Their nitrile coating also makes these safety gloves particularly hard-wearing, boasting EN level 4 abrasion resistance
- **Elevated comfort:** Manufactured with a seamless nylon liner, these liquid-repellent HyFlex® gloves grant wearers high levels of dexterity and comfort
- **Food handling compliance:** In addition, they are suitable for varied food processing applications
- **Minimized health risks:** They are also Oeko-Tex®-certified as free of substances potentially harmful to human health, such as DMF



Industries

- Agriculture
- Machinery and Equipment
- Construction
- Food Processing

Applications

- Assembly of white goods
- Maintenance
- Preparation of site - unloading of lines and valves
- Metal Fabrication
- General handling
- Quality control

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-919

High flexibility and dexterity for an optimum comfort in use

Key Features

- **Liquid-repellent design:** Liquid, oil, grease and dirt protection
- **Full nitrile coating:** Superb abrasion resistance
- **Seamless nylon liner:** Natural fit, for added comfort and dexterity

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)
- Zinc Dibutyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



EN388: 2016



4121A



STANDARD

100

4419CIT
CITEVE

Technologies



DMF free



STANDARD
100

4419CIT
CITEVE

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-919	Finishing: Fully Coated Coating Material: Nitrile Liner Material: Nylon Cuff Style: Knitwrist	13	6, 7, 8, 9, 10	220-260 mm	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell