

SOL-ES-PRO-RF - Sensor

1074978

<https://www.phoenixcontact.com/in/products/1074978>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Lambrecht Meteo GmbH precipitation sensor with weighing technology, for measuring precipitation amounts and intensities, unheated. The measured value is provided via Modbus/RTU (RS-485).

Product description

All "Solarline Environment Sensors" (SOL-ES) are used with the Phoenix Contact weather station via Plug and Play (see accessories). They are especially suitable for capturing weather data in photovoltaic systems.

To mount the sensor, a separate stainless steel mast can be purchased from Lambrecht Meteo GmbH or another manufacturer.

Your advantages

- Electronically controlled heating with separate heating circuit
- Overflow-proof weighing technology
- Corresponds to IEC 61724-1, Class A (highest precision)

Commercial data

Item number	1074978
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	*****
Product key	DTHAAA
GTIN	4055626777818
Weight per piece (including packing)	500 g
Weight per piece (excluding packing)	100 g
Customs tariff number	90158020
Country of origin	DE

SOL-ES-PRO-RF - Sensor

1074978

<https://www.phoenixcontact.com/in/products/1074978>



Technical data

Notes

Note regarding documentation	For technical data, see the item-specific data sheet in the "Downloads" area
------------------------------	--

Product properties

Product type	Sensor
--------------	--------

SOL-ES-PRO-RF - Sensor

1074978

<https://www.phoenixcontact.com/in/products/1074978>



Classifications

ECLASS

ECLASS-11.0	27143137
ECLASS-12.0	27143137
ECLASS-13.0	27143137

ETIM

ETIM 9.0	EC000926
----------	----------

UNSPSC

UNSPSC 21.0	43201500
-------------	----------

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-7
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

SOL-ES-PRO-RF - Sensor

1074978

<https://www.phoenixcontact.com/in/products/1074978>



Accessories

SACC-M12MS-5PL M - Connector

1424649

<https://www.phoenixcontact.com/in/products/1424649>



Connector, Universal, 5-position, unshielded, Plug straight M12, coding: A, Push-lock spring connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4 mm ... 8 mm

SAC-5PY-F/M-F VP SH - Y distributor

1419933

<https://www.phoenixcontact.com/in/products/1419933>



Y distributor, 5-position, shielded, Socket straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A and Plug straight M12 SPEEDCON, coding: A, Parallel distributor

SOL-ES-PRO-RF - Sensor

1074978

<https://www.phoenixcontact.com/in/products/1074978>



SAC-5P-M12MS/ 0,3-PUR/M12FS SH - Sensor/actuator cable

1500884

<https://www.phoenixcontact.com/in/products/1500884>



Sensor/actuator cable, 5-position, PUR halogen-free, black-gray RAL 7021, shielded (Advanced Shielding Technology), Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 0.3 m

SAC-5P-M12MS/ 0,6-PUR/M12FS SH - Sensor/actuator cable

1500897

<https://www.phoenixcontact.com/in/products/1500897>



Sensor/actuator cable, 5-position, PUR halogen-free, black-gray RAL 7021, shielded (Advanced Shielding Technology), Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 0.6 m

SOL-ES-PRO-RF - Sensor

1074978

<https://www.phoenixcontact.com/in/products/1074978>



SAC-5P-M12MS/ 1,5-PUR/M12FS SH - Sensor/actuator cable

1500907

<https://www.phoenixcontact.com/in/products/1500907>



Sensor/actuator cable, 5-position, PUR halogen-free, black-gray RAL 7021, shielded (Advanced Shielding Technology), Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 1.5 m

SAC-5P-M12MS/ 3,0-PUR/M12FS SH - Sensor/actuator cable

1500910

<https://www.phoenixcontact.com/in/products/1500910>



Sensor/actuator cable, 5-position, PUR halogen-free, black-gray RAL 7021, shielded (Advanced Shielding Technology), Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 3 m

SOL-ES-PRO-RF - Sensor

1074978

<https://www.phoenixcontact.com/in/products/1074978>



WP-PA HF 13,0 BK - Protective hose

3240681

<https://www.phoenixcontact.com/in/products/3240681>



Protective hose, material: PA 6, UV-resistant: yes, flexible, degree of protection: IP68, color: black, flammability rating in acc. with UL 94: V0, inside diameter: 10 mm, Total length: 50 m

SOL-SC-WTH-STN - Weather station

1322110

<https://www.phoenixcontact.com/in/products/1322110>



Weather station for acquiring measured data from connected environmental sensors. Together with SOL-ES sensors, it can be used in PV parks or other industrial areas, for example. The measured data is made available to the user via a user interface and transmitted to a higher-level data management system.

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in