

## FEATURES

- Quick and easy installation
- Available in red or amber
- Powerful flashing signal light
- Snap fit mounting plate design
- Ideal for use both indoors and outdoors

## RS PRO Amber Xenon Beacon, 10 → 30 V dc, Flashing, Magnetic

RS Stock No.: 235-584



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

These Xenon Beacons from our own RS PRO brand are high quality flashing beacons ideal for use in wide range of applications requiring a low cost and energy efficient signalling solution. The snap fit design of the mounting plates allows you to install the xenon beacons with ease, with one plate being attached to the beacon and the other to the surface. This range of flashing beacons from RS PRO are suitable for light and heavy industrial signalling applications, producing a powerful flashing light source to signal hazards and emergencies.

### General Specifications

<b>Nominal flash rate</b>	75 per minute
<b>Bulb Type</b>	Xenon
<b>Light Effect</b>	Flashing
<b>Lens Colour</b>	Amber
<b>Fitting</b>	2clamp nuts
<b>Magnetic type</b>	Yes
<b>Housing Colour</b>	Black
<b>Lamp Include</b>	Yes
<b>Multifunction</b>	No
<b>Number of LED</b>	1
<b>Special Features</b>	Low Profile & Compact Design

### Electrical Specifications

<b>Supply Voltage</b>	10VDC to 30VDC
<b>Current Type</b>	DC
<b>Current Consumption</b>	150mA , 175mA

**Mechanical Specifications**

<b>Dimensions</b>	130mm (h)
<b>Base Diameter</b>	150mm
<b>Mounting Style</b>	Magnetic

**Operation Environment Specifications**

<b>Maximum Temperature</b>	-30°C
<b>Minimum Temperature</b>	+50°C

**Protection Category**

<b>IP Rating</b>	IP 56
------------------	-------

**Approvals**

<b>Standards Met</b>	EMC (ECE R10), RoHS Compliant
----------------------	-------------------------------

