



## RECIPROCATING SAW, CAPACITY

1.6MM

**RC312SET**

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:44





**DESCRIPTION**

**RECIPROCATING SAW, CAPACITY 1.6MM**

Saw designed for cutting thin sheet metal, notably for bodywork and general maintenance. Aluminium body. Adjustable stop. Variable speed control. Silent ducted exhaust. Speed of 9,000 strikes per minute. Supplied with a set of saw blades (Ref. RA31324SET and RA- 31332SET - 24 and 32 teeth)

**SPECIFIC DATA**

Designation	RECIPROCATING SAW CAP 1.6MM
Sales reference	RC312SET
L (mm)	235
Weight (g)	820

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



I (mm)	39
H (mm)	70
Capacity (mm)	1.6
Vibration (m/s <sup>2</sup> )	51
Noise level (dBa)	91
C mm	6,3
C min mm	360
C mm	1/4
C mm	9 000
Guarantee	M2   SAM Equipment and Machine Guarantee

**Guarantee applied**

**M2 | SAM Equipment and Machine Guarantee**

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

>> [Find out more](#)

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:44

