

Robust neoprene gloves, granting excellent, all-round mechanical and chemical protection

- **Heightened protection:** AlphaTec® 09-022 heat and cold-resistant gloves feature a special Hi-Lo insulated gauntlet option with quilted cotton liner for use in both hot and cold conditions, allowing intermittent handling in hot liquids up to 180°C and in cold temperatures down to -25°C
- **Advanced ergonomics:** The anatomical shape of these heavy-duty, black chemical gloves is designed to follow hand contours, improving dexterity and alleviating hand fatigue
- **Improved features:** In addition, AlphaTec® 09-022 hand protection gloves offer excellent broad-spectrum chemical resistance, protecting against oils, acids, caustics, alcohols and solvents, while their cotton lining enhances snag and puncture resistance

**Caution: Do not use the 09-022 gloves in applications above 180°C (400°F)*

Industries

- Metal fabrication
- Chemical
- Automotive Aftermarket
- Machinery and Equipment

Applications

- Foundry operations
- Handling materials with sharp or rough edges
- Extruding, bending and punching shapes
- Processing sheets, coils, tubes
- Fabricating metal parts, glass sheets
- Unexpected leakages spills or other releases



Previously known as: Scorpio™ 09-022

Key Features

- **Special Hi-Lo insulated gauntlet option:** For hot and cold conditions
- **Anatomical shape:** For protective gloves with improved dexterity
- **Smooth finish:** Optimal defense against mechanical and chemical hazards

Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 09-022	Liner Material: Cotton Jersey Coating Material: Neoprene	10	350 / 13.8	Black	• 12 pairs in a bag, 3 bags in a carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.