

Hedge Trimmer XGT®

UH014G

40Vmax • 750 mm

Efficient brushless Trimmer for professional use.

Professional XGT® Hedge Trimmer with brushless motor. The blade is single-sided for a lightweight and ergonomic design.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	2000 / 3600 / 5000 min ⁻¹
Length Of Blade	750 mm
Max blade opening	23,5 mm
Tooth Spacing	35 mm
Continuous Use XGT® 40V Max / 4.0 Ah	80 / 155 / 380
Brushless Motor	✓
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	3,2 / 2,5 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²

User benefits

- Reverse rotation system frees the blade when it is jammed by thick branches
- Optimum blade shape for smooth cutting and long run time
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing