

LONG LIFE FINISHING METAL

EXPERT N880 Fleece Disc

EXPERT

- ① Strong, flexible bonding with Bosch Surface Structure
- ② 3D structure allows grit through the fleece
- ③ Consistent cut and finish with cross-laying technology



**SURFACE
STRUCTURE**

**UP TO
3x***

LONG LIFE

* vs. Bosch J475



Video



BOSCH

EXPERT N880 FLEECE DISC



- Ideal for cleaning stainless steel, for example to achieve a final surface finish; for light deburring and surface blending
- Best for metalworkers: Long Lasting Quality
- Lasts up to 3x longer than Bosch J475 coated hand sanding sheet
- Just stick it on with hook and loop



PRODUCT PROPERTIES				ORDERING INFORMATION					
Grade	Diameter mm	Product colour	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number		
Cleaning	125	white	C0a	1	20	572 093	2 608 901 240		
Extra cut A	125	brown	C0a	1	20	572 109	2 608 901 241		
Medium S	125	black	C0a	1	20	572 116	2 608 901 242		
Medium A	125	maroon	C0a	1	20	572 123	2 608 901 243		
Very fine A	125	maroon	C0a	1	20	572 130	2 608 901 244		
Ultra fine S	125	grey	C0a	1	20	572 147	2 608 901 245		
Very fine GP	125	green	C0a	1	20	572 154	2 608 901 246		
Cleaning	150	white	C0a	1	20	572 161	2 608 901 247		
Extra cut A	150	brown	C0a	1	20	572 178	2 608 901 248		
Medium S	150	black	C0a	1	20	572 185	2 608 901 249		
Medium A	150	maroon	C0a	1	20	572 192	2 608 901 250		
Very fine A	150	maroon	C0a	1	20	572 208	2 608 901 251		
Ultra fine S	150	grey	C0a	1	20	572 215	2 608 901 252		
Very fine GP	150	green	C0a	1	20	572 222	2 608 901 253		
Extra cut A	125	brown	P0f	5	4	584 249	2 608 901 385		
Medium A	125	maroon	P0f	5	4	584 256	2 608 901 386		
Ultra fine S	125	grey	P0f	5	4	584 263	2 608 901 387		
Extra cut A	150	brown	P0f	5	4	584 270	2 608 901 388		
Medium A	150	maroon	P0f	5	4	584 287	2 608 901 389		
Ultra fine S	150	grey	P0f	5	4	584 294	2 608 901 390		



BOSCH