



Technical data

51318

One direction thrust ball bearings

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	90 mm
D - External diameter	155 mm
T - Thrust bearing height	50 mm
rs - Min fillet radius	1,5 mm
Mass	3,74 kg

PRODUCT PERFORMANCE

Ca - Dynamic axial load rating	213000000 mN
C0a - Static axial load rating	525000000 mN
Cua - Limit axial load rating	21300000 mN
N lim - Oil lubrication limit speed	9600 °/s
N lim - Grease lubrication limit speed	6600 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

Da max - Max shoulder diameter OR	116 mm
da min - Min shoulder diameter IR	129 mm

