

## Protective hose - WP-PA HF-HB 28,5 BK - 3240842

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Polyamide protective hose, inflammability class HB, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

Image shows WP-PA HF-HB 10.0  
BK version



### Key commercial data

Packing unit	50 M
Minimum order quantity	50 M
GTIN	 4 046356 736589
Weight per Piece (excluding packing)	99.99 g
Custom tariff number	39173200
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Inner diameter (f)	23.00 mm
Outside diameter	28.50 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Short-term temperature	120 °C

#### General

Color	black
Type	Helically corrugated plastic hose
Components	free from silicone, halogen, and cadmium
Inflammability class according to UL 94	V0
Material	PA
Bending radius, static	55.00 mm

# Protective hose - WP-PA HF-HB 28,5 BK - 3240842

## Technical data

### General

Bending radius, dynamic	100.00 mm
-------------------------	-----------

## Classifications

### eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Approvals

### Approvals

#### Approvals

UL Recognized / VDE Zeichengenehmigung


#### Ex Approvals


#### Approvals submitted

#### Approval details

## Protective hose - WP-PA HF-HB 28,5 BK - 3240842

### Approvals

UL Recognized 

VDE Zeichengenehmigung 

### Accessories

#### Accessories

##### Corrugated pipe screw connection

Screw connection - WP-G HF IP66 PG21 BK - 3240892



Cable gland, Pg thread, IP66 protection, straight

Screw connection - WP-G HF IP66 M25 BK - 3240899



Cable gland, metric thread, IP66 protection, straight

Screw connection - WP-G HF IP69K PG21 BK - 3240878



Cable gland, Pg thread, IP68/69k protection, straight

Screw connection - WP-G HF IP69K M25 BK - 3240885



Cable gland, metric thread, IP68/69k protection, straight

## Protective hose - WP-PA HF-HB 28,5 BK - 3240842

### Accessories

Screw connection - WP-GA HF IP66 PG21 BK - 3240920



Cable gland, Pg thread, IP66 protection, angled

Screw connection - WP-GA HF IP66 M25 BK - 3240927



Cable gland, metric thread, IP66 protection, angled

Screw connection - WP-GA HF IP69K PG21 BK - 3240906



Cable gland, Pg thread, IP68/69k protection, angled

Screw connection - WP-GA HF IP69K M25 BK - 3240913



Cable gland, metric thread, IP68/69k protection, angled

Screw connection - WP-GR HF IP66 PG21 BK - 3240948



Cable gland, Pg thread, IP66 protection, with strain relief

## Protective hose - WP-PA HF-HB 28,5 BK - 3240842

### Accessories

Screw connection - WP-GR HF IP66 M25 BK - 3240955



Cable gland, metric thread, IP66 protection, with strain relief

---

Screw connection - WP-GR HF IP69K PG21 BK - 3240934



Cable gland, Pg thread, IP68/69k protection, with strain relief

---

Screw connection - WP-GR HF IP69K M25 BK - 3240941



Cable gland, metric thread, IP68/69k protection, with strain relief

---

### Mounting material

Hose holder with cover - WP-BASE C PA HF 28,2 BK - 3240962



Hose holder with cover

---

Hose clamp - WP-BASE HF 29 - 3240971



Hose clamps

## Protective hose - WP-PA HF-HB 28,5 BK - 3240842

### Accessories

Protective hose fixing bracket - WP-BASE A PG21 - 3241080



Fixing bracket for protective sleeves, fixed with two screws

---

### Protective cap

Transition sleeve from hose to cable - WP-EC TPE HF 28,5 BK - 3240978



End sleeves, transition sleeves, from hose to cable

---

Cable protection end sleeve - WP-SC PA HF 28,5 BK - 3240985



End sleeves as cable protection