

Datasheet

Filament Indicator Lamp

RS Stock number 104-755



Specification

Structure		Design Characteristics	
Bulb Type	T10X28	Voltage	100V
Bulb Diameter	Ø10.0 Max	Amperage	2.5mA \pm 10%
Length	28.0 Max	Life Hours	50,000 Hours
Base Type	Ba9s	Gas Type	Neon Gas Filled