



560.1683

INTERLOCKED SOCKET

16A 2P+E 6h 200-250V 50Hz 60Hz

106X240MM Screw terminals With mechanical interlock

Product Approvals

TECHDATA		STANDARDS AND LAWS	
Commercial series	ADVANCE 2 Series	EN 60309-1 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Type of product	INTERLOCKED SOCKET	EN 60309-2 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Synthetical description	INTERLOCKED SOCKET		
Mounting version	SURFACE MOUNTING		
Rated current	16A	EN 60309-1/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Poles	2P+E	EN 60309-2/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Hour position	6h		
Rated voltage (range)	200-250V	EN 60309-4 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Switched socket-outlets and connectors, with or without interlock
Rated voltage	200-250V		
Working frequency	50Hz	EN 60309-1/A2 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Working frequency	60Hz	EN 60309-2/A2 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Colour	BLUE		
Material	THERMOPLASTIC		
Protection degree	Splash proof	EN 60309-4/A1 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. - Switched socket-outlets and connectors, with or without interlock
Protection degree IP	IP44		
Protection degree IK	IK07	DIRECTIVE LOW VOLTAGE 2014/35 /UE	[European Directives] Low Voltage Directive
Terminals	Screw terminals		
Flange	106X240MM		

Cable outlet	M25X1,5
Options	With mechanical interlock
Notes	WITHOUT FUSE HOLDER
Padlock	ø5mm