


# push-in sleeve QSH-12-8

Part number: 130627

FESTO

reducing.



## Data sheet

Feature	Value
Size	Standard
Nominal size	4.9 mm
Assembly position	Any
Container size	10
Design structure	Push/pull principle
Operating pressure complete temperature range	-0.95 ... 6 bar
Temperature dependent operating pressure	-0.95 ... 14 bar
Maritime classification	see certificate
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 ... 80 °C
Product weight	2.1 g
Pneumatic connection, port 1	Push-in sleeve QS-12
Pneumatic connection, port 2	Push-in sleeve QS-8
Colour of release ring	blue
Materials note	Conforms to RoHS
Material housing	PBT
Material release ring	POM