



## DCS373M2

### 18V XR Li-Ion Metal Cutting Circular Saw

#### Selling Proposition

- Powerful & highly efficient PM58 DEWALT fan-cooled motor with replaceable brushes delivers up to 3700 rotation per minute for fast cutting action
- Ergonomic handle set with rubber overmould to optimise end user comfort
- Extremely durable tool design with steel shoe to withstand rough job site conditions
- Intelligent variable speed trigger
- Lock off switch and electronic motor brake for additional control and work safety
- New transparent front guard paired with LED light and the unique chemically treated glass window for enhanced line of cut visibility

#### Standard Equipment

- 140 mm tungsten carbide blade
- Hex key
- Multi-voltage charger
- 2 x 4.0Ah XR Li-Ion battery packs with state of charge indicator
- Heavy duty kit box

#### Warranty Specifications

- 3 year limited warranty
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

Specifications	
Battery chemistry	XR Li-Ion
Voltage	18 V
Kapazität	4.0 Ah
Blade Diameter	140 x 20 mm
Abgabeleistung	460 Watt
No Load Speed	3700 rpm
Max. Depth of Cut at 90°	43 mm
Gewicht	3.8 kg