


GigaDuct Elbow, Vertical Down, 90°, 50mm, No Cover

Art.-Nr. 855-05065 | LG-BVOD90-YL-N 



- 50mm wide
- 90° Bend
- Supplied without cover
- For creating vertical downward routing transitions from horizontal routes
- Fully encloses cables to keep out dirt and dust as the fibre is routed through different areas of the data centre
- Protects cables by maintaining proper bend radius, preventing micro bends and macro bends that degrade performance
- it



More products in this product group:

[Fittings >](#)



Application	vertical outside elbows are used for creating a vertical downward transition from GigaDuct horizontal routes. This model offers a 90° bend and is supplied without cover.
Colour	Yellow (YE)
PART DESCRIPTION	LG-BVOD90-YL-N
Product Family	Elbow - Vertical Outside
Product Group	Fittings
Short Description	GigaDuct Elbow, Vertical Down, 90°, 50mm, No Cover
Technical Description	GigaDuct is a robust, scalable cable management system engineered specifically for organising and protecting optical fibre cables in the data centre environment. Constructed with precision, it provides a dedicated pathway that prevents cable congestion, minimises physical stress on fibres, and facilitates efficient cable management. Whether you are setting up a new data centre or upgrading an existing one, HellermannTyton’s GigaDuct offers unmatched versatility and reliability.
Type	LG-BVOD90-YL-N

Product Dimensions

Angle	90
-------	----

Specifications

Halogen-free	Yes
Limited Fire Hazard	Yes
ROHS compliant	Yes
Specifications	HF LFH RoHS

Logistics and Packaging

Country of Origin	GB
GTIN-13 / EAN	5022660242007

More Information

