

# Drill Driver LXT®

## DDF083

18V • 40 Nm • 0 – 1 700 min<sup>-1</sup>

### Small and light brushless screwdriver

A light and compact brushless screwdriver for fitters and maintenance staff and for home use. Thanks to its small size, this tool is easy to use and offers access to tight places. A max. torque of 40 / 23 Nm and two speed ranges. Integrated LED light.



### Technical specifications

|                                                       |                                      |
|-------------------------------------------------------|--------------------------------------|
| Nominal Battery Voltage                               | 18 V                                 |
| Voltage LXT                                           | ✓                                    |
| Brushless Motor                                       | ✓                                    |
| No load speed                                         | 0 - 500 / 0 - 1700 min <sup>-1</sup> |
| Max. fastening torque Hard/Soft                       | 40 / 23 Nm                           |
| Max Torque                                            | 40 Nm                                |
| Torque setting                                        | 20                                   |
| Max. Drilling Diameter in Wood                        | 36 mm                                |
| Max. Drilling Diameter in Steel                       | 13 mm                                |
| Driving Shank                                         | 1/4 "                                |
| Drilling Capacity Wood (Auger Bit)                    | 36 mm                                |
| Drilling Capacity Wood (Self-feed bit)                | 72 mm                                |
| Vibration Level, Drilling into metal                  | ≤ 2,5 m/s <sup>2</sup>               |
| Vibration Uncertainty (K Factor), Drilling into metal | 1,5 m/s <sup>2</sup>                 |
| Sound Pressure Level (L <sub>pA</sub> )               | 77 dB(A)                             |
| Noise Uncertainty (K Factor)                          | 3 dB(A)                              |

### User benefits

- Extremely compact thanks to a brushless motor
- Low power consumption thanks to brushless motor
- LED light illuminates the work site
- Ideal for working in tight spaces and overhead applications
- The rubber coating on the handle ensures a firm working grip
- Battery protection system automatically shuts off power when the battery level is low
- Quick mount for 1/4 "screwdriver

Link to product - [www.makitauk.com](http://www.makitauk.com)



# Related products

## Other

User manual

Parts drawing