



ENGLISH

## Datasheet

# RS Wall Volume Controller, 20W

RS Stock 406-0905



### Specification:

|                           |                  |
|---------------------------|------------------|
| Line voltage              | 100v             |
| Power rating              | 20w              |
| Switch positions          | 11 + off         |
| Attenuation per step      | 3dB*             |
| Total attenuation         | 36dB             |
| Insertion loss            | less than 0.5dB  |
| Relay spec. (both models) | Coil 24v DC 22mA |
| Plate size                | single gang      |
| Dimensions (H X W x D)    | 124 x 70 x 42.5  |