

## Axial cylindrical roller bearings 81105-TV (Series 811)

single direction, comprising K811, GS, WS

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

d	25 mm
D	42 mm
T	11 mm
D <sub>1</sub>	26 mm
d <sub>1</sub>	42 mm
Da max	26 mm
da min	41 mm
r <sub>a</sub> max	0,6 mm
r <sub>min</sub>	0,6 mm
m	0,053 kg    Mass

$C_a$	33500 N	Basic dynamic load rating, axial
$C_{0a}$	76000 N	Basic static load rating, axial
$C_{ua}$	7200 N	Fatigue limit load
$n_G$	8900 1/min	Limiting speed
$n_{\theta r}$	3650 1/min	Reference speed
	K81105-TV	Allocated axial cylindrical roller and cage assembly
	GS81105	Allocated housing locating washer
	WS81105	Allocated shaft locating washer
	LS2542	Allocated bearing washer



