

TECHNICAL DATA
ONE-WRAP #29

(EUROPEAN)

Construction

Base material Polypropylene & velour PA
Construction Extruded and laminated

Width Nominal $\pm 1\%$
Hooks/cm² (type #29) $266 \pm 10\%$
Overall thickness $1.35 \pm 0.20\text{mm}$
Weight/m² $550\text{g/m}^2 \pm 60\text{g/m}^2$

Colours: White, Black, Yellow, Green, Blue, Red
Hook colours: Natural except for black and white where the hook is black or white

Performance

Peel Strength* Minimum 0.4 N/cm
Shear Strength* Minimum 7.0 N/cm²
Cycle Life* 50% loss after 100 cycles
Breaking strength* Minimum 120 N/cm
Melting Point 150°C

Resistance Properties

Electrical Insulator None
Washing Resistance Good
UV Resistance Low
Humidity Resistance Medium
Sewn Resistance Low
Acid Resistance Medium

* Internal Norm of VESA

The information in this Technical Sheet is based on reliable tests and trials. Given the diversity of the use of our products we advise our customers to ensure themselves that the product meets the requirements of their application. The responsibility for the application and use of the product remains with the customer.

FTP 601 Revision 0° Edition 1^a of 01/00



VELCRO LTD
1 Aston Way
Middlewich
Cheshire CW10 0HS
Sales & Customer Service: 01606 738744
Customer Service Fax: 01606 738813
General Switchboard: 01606 738806
General Fax: 01606 738814
Email: enquiries@velcroltd.demon.co.uk