

## FEATURES

- This heavy-duty, multi-purpose RS PRO shelf trolley is a steady and strong unit
- Powder-coated for resilience and durability
- Fully-welded steel frame ensures strength and durability
- Handles to assist manoeuvrability and handling
- Removable containers offer a secure method of storage and transportation

## RS PRO 6 Shelf Steel Drawer Trolley, 600 x 400 x 200mm, 250kg Load

RS Stock No.: 877-6806



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

Introducing the range of RS PRO Shelf Trolleys, ideal for transporting items in factories, warehouses and much more. The robust trolleys are designed to look professional in any setting they are used and offer a powder-coated finish that's easy to keep clean, handy when in use within industrial environments. The fully welded steel frame ensures durability and strength while offering optimum storage and transport capacity with shelves for containers. With a 250 kg load capacity, a heavy-duty frame, two fixed and two swivel rubber cushion wheels, this RS PRO trolley is an ideal investment that is versatile enough to be used across a wide range of applications.

What other trolleys are available in this RS PRO range?

877-6806 6 Shelf Trolley with 40 L Containers, Unbraked, 600mm x 400mm x 200mm

877-6809 6 Shelf Trolley with 40 L Containers, Braked, 600mm x 400mm x 200mm

877-6792 6 Shelf Trolley with 30 L Containers, Unbraked, 600mm x 400mm x 170mm

877-6796 6 Shelf Trolley with 30 L Containers, Braked, 600mm x 400mm x 170mm

877-6780 8 Shelf Trolley with 22 L Containers, Unbraked, 600mm x 400mm x 120mm

877-6799 8 Shelf Trolley with 22 L Containers, Braked, 600mm x 400mm x 120mm

### General Specifications

<b>Type</b>	Drawer
<b>Weight Class</b>	Medium Duty
<b>Number of Levels</b>	6
<b>Wheel Type</b>	Rubber
<b>Wheel Features</b>	Swivel
<b>Folding shelf</b>	No
<b>Frame Material</b>	Steel
<b>Wheel Material</b>	Vulcanised Rubber
<b>Brakes</b>	No
<b>Applications</b>	Warehouses, Commercial workshops and garages, Workshops or garages at home, Catering and food industry, Schools, Shops

### Mechanical Specifications

<b>Load Capacity</b>	250kg
<b>Wheel Diameter</b>	100mm

Trolley Size	
Dimension	1500mm x 700mm x 470mm
Depth	700mm
Width	470mm
Height	1500mm

External Shelf Size	
Platform Dimension	600mm x 400mm x 200mm
Platform Length	600mm
Platform Width	400mm

Internal Shelf Size	
Dimension	552mm x 353mm x 185mm
Length	552mm
Width	353mm

Description	Euro Container Size - L x W x L (mm) / No. of Containers Per Trolley			Unbraked / Braked Castors	RS Stock No.
	External-600x400x120	External-600x400x170	External-600x400x200		
	Internal-555x358x105	Internal-560x360x157	Internal-552x353x185		
8 Tier Trolley	8	-	-	Unbraked	877-6780
	8	-	-	Braked	877-6799
6 Tier Trolley	-	6	-	Unbraked	877-6792
	-	6	-	Braked	877-6796
	-	-	6	Unbraked	877-6806
	-	-	6	Braked	877-6809