



FLAMESTAT HIGH VIS JACKET CLASS 3 4175 ATHS

ART. NO: 119922

Dirt, oil and water-repellent / Reflective detailing on shoulders / Front placket opening with zip to top of collar and concealed snap fastening / Bellowed chest pocket with concealed snap fastening, inside D-ring and pen strap / Chest pocket with zip / Concealed buttons and loops for sheath knife / Microphone holder / 2 front pockets with zip / Inside pocket with button / Inside mobile phone pocket with velcro fastening and loop for mobile phone earpiece / Adjustable cuffs with snap fastening / Adjustable drawstring at hem / Extended back / Approved according to EN 61482-1-2 APC 1, EN 61482-1-1 ELIM: 9 cal/cm² (see Electric arc table for certified garment combinations for EN 61482-1-2 class 2 and open arc according to EN 61482-1-1), EN ISO 11612 A1 A2 B1 C1 E2 F1, EN ISO 11611 A1 A2 class 1 (see Flame and welding table for certified garment combinations), EN 1149-5, EN 13034 Type PB [6] and EN ISO 20471 class 2 in size XS and class 3 in sizes S-3XL / Certified after 50 washes / Leasing laundry-tested according to ISO 15797 / OEKO-TEX® certified.

Material: 45% modacrylic, 35% cotton, 18% polyamide, 2% anti-static fibre. Inherent flame protection. In transition to PFAS free.

Weight: 300 g/m².

Color: F171 High vis Yellow/Navy

Size: XS-4XL



EN 11612



EN 11611



EN 1149-5



IEC 61482-2



EN 13034



EN 20471



FRISTADS®

SIZES MAY VARY BETWEEN COLORS
Print date: 2025-09-04