

M18 POALC-O | M18™ PACKOUT™ area light charger



- Three independent pivoting light heads provide 3000 lumens of TRUVIEW™ High Definition Output
- All three pivot light heads combined provide up to 12 hours of run time on a M18™ REDLITHIUM™ 5.0 Ah battery pack
- IP54: water and dust resistant
- Built in charger function for quick and convenient charging of any M18™ battery or electric devices via the 2.1 AMP USB output port
- Full system compatibility with the PACKOUT™ Modular Storage System – lighting on and off the stack
- AC/DC versatility: Powered by MILWAUKEE® M18™ batteries, or mains plug supply
- Storage compartment for devices and small items

Max. light output high / medium / low / strobe (lumens)	3000/ 1500/ 1000/ -
---	---------------------

Max. run time with M18 B5 battery (h)	12/ 8/ 4/ -
---------------------------------------	-------------

Weight with battery pack (EPTA) (kg)	5.9 (M18 B5)
--------------------------------------	--------------

Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
--------------	---

Article Number	4933478120
----------------	------------