



ENGLISH

Datasheet

RS Pro Panel Mount, PCB Slide Switch

Stock No: 665-332



Product Details

RS Pro DPDT slide switch withstands currents up to 500 A at 125 V ac voltage. This PCB, panel mount switch performs on-on operation. The snap slide-action switch has silver plated contacts for added durability.

Features and Benefits

- Snap slide-action switch
- Silver plated contacts
- Connections to solder tags

Specifications

Contact Configuration:	DPDT
Mounting Type:	Panel Mount, PCB
Switch Operation:	On-On
Contact Current Rating:	0.5 A @ 125 V ac
Terminal Type:	Solder
Actuator Type:	Slide
Length:	36mm
Width:	13.5mm
Depth:	7mm
Dimensions:	36 x 13.5 x 7mm
Contact Resistance:	20mΩ
Mechanical Life:	10000Operations
Minimum Operating Temperature:	-10°C
Maximum Operating Temperature:	+60°C
Operating Temperature Range:	-10 → +60°C
Contact Material:	Silver
Voltage Rating:	125V ac