

KERN IXC 60K-3

KERN

Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation



Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	IXC

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Number of weighing ranges	1
Weighing capacity [Max]	60 kg
Readability [d]	0,002 kg
Reproducibility	0,002 kg
Linearity	± 0,006 kg
Resolution	30.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	60 kg (M1)
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,01 kg
Maximum creep (15 minutes)	8 g
Maximum creep (30 minutes)	16 g
Default unit	kg
Units	kg
	g
	lb
	ffa
	PCS
	%
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	4-wire

Display

Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display screen size	160×60 mm
Display segments	6
Display digit height	48 mm
Languages of the user interface	English Symbol language

Construction

Dimension display device (W×D×H)	232×150×77,3 mm
Dimensions weighing surface (W×D)	400×300 mm
Dimensions weighing surface	400×300 mm
Dimensions weighing platform (W×D×H)	400×300×117 mm
Material weighing plate	stainless steel
Material platform	steel, powder-coated
Material display housing	stainless steel
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Stand rotatable	no
Stand inclinable	no
Wall mount	✓
Display device cable length	3 m
Allowed cable length display device [Max]	3 m
Platform Construction	Single-Cell
Load cells - number	1

Functions

PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	30.000

KERN IXC 60K-3



Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation

Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	2 g
Smallest piece weight when piece counting - normal conditions	20 g
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Hold function	✓
IP protection - complete device	-
IP protection - display	IP68
IP protection - platform	no IP protection
IP protection - load cell	IP65
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
Auto-off interval(s) in mains power mode	30 sec
	off
Tare function	manual (multi)
Number of keys for operation	7

Interface

Interfaces	RS-232 (optional, factory)
	Ethernet (optional, factory)
	WiFi (optional, factory)
	Alibi memory (optional, factory)
	analogue (0 - 10 V) (optional, factory)
	analogue (4 - 20 mA) (optional, factory)
	Bluetooth BLE (v4.0) (optional, factory)
	USB-Device (optional, factory)
	EasyTouch (ET) - Compatibility
	vollständig
EasyTouch (ET) - Connection type	
KUM	

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Input voltage power supply / power [Max]	110 V - 240 V AC

Battery / accumulator type	Li-Ion
Battery	no battery
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional (factory)

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	465×790×220 mm
Net weight	6,8 kg
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	10 kg
Shipping weight	16,2 kg


KERN IXC 60K-3



Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation

Pictograms

STANDARD



OPTION



FACTORY

