



Part Number : [1300170058](#)
Product Description : Mini-Change Field Attachable, Male Connector, 4 Pole, Cable Range: 5.08-12.19mm Outside Diameter with External Threads
Series Number : 130017
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : 1A4006-34PWR




Documents & Resources

Drawings
[1300170058_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130017
Description	Mini-Change Field Attachable, Male Connector, 4 Pole, Cable Range: 5.08-12.19mm Outside Diameter with External Threads
Approvals	cULus Listed
IP Rating	IP67
Product Name	Mini-Change
Type	Field Attachable Connector
UPC	887191426433

Agency

UL	E258922
----	---------

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	600V AC/DC

Physical

Cable Diameter	5.00 - 12.00mm (.197-.472")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	Nylon
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass

Material - Plating Mating	Gold
Net Weight	54.800/g
Orientation	Straight
Poles	4
Temperature Range - Operating	-20°C to +80°C
Wire Size (AWG)	15 to 24