

Datasheet

RS Pro 2.54mm Pitch Straight PCB Terminal Block with Spring Cage Termination, Through Hole, 1 Way

RS Stock No: **790-1121**



Product Details

RS Pro 2.54 mm pitch PCB terminal block comes with spring cage termination. It can be hole mounted and has 1-way contact. A professional range of 1-way PCB Spring Terminal Blocks for 20-26 AWG wire with 2.54 mm pitch. These 2.54 mm pitch PCB spring terminal blocks have rectangular tin plated PC tails which are 0.8 x 0.5 mm by 3.5 mm long.

Specifications:

Body Orientation	Straight
Colour	Green
Current Rating	6 A
Depth	13.6 mm
Gender	Female
Length	5.54 mm
Material	Nylon 66
Mounting Type	Through Hole
Number of Contacts	1
Number of Rows	1
Pitch	2.54 mm
Termination Method	Spring Cage
Type	PCB Terminal Block
Voltage Rating	150 V
Width	13.6 mm
Insulation Resistance	>2000 mΩ
American Wire Gauge	20 to 26 AWG
Insulation Withstand Voltage	2000 V ac
Operating Temperature Range	-40 to +105°C
Flammability Rating	UL 94 V-0