

M12 360IC12-OC

M12™ 360° INSPECTION CAMERA 1.2 M 2ND GEN

- 4.3" LCD screen delivers sharp and clear images and allows users to see objects in greater detail
- 270° rotating screen provides the user fluid image control in every position of use
- 1.2 metre cable balances flexibility and rigidity for both drain line and behind wall inspections
- Included 32 GB micro SD card allows to record and store images and videos
- 5 modes of brightness provide best in class illumination without shadow or glare
- 10 mm camera head for easy access in tight spaces
- 720p camera resolution provides outstanding image quality
- 3 level zoom to quickly focus on points of interest
- Digital 180° image rotation to easily adjust the perspective
- IP67 camera head and camera cable withstands toughest jobsite conditions
- Included hook, magnet, mirror and plumbing ball attachments for added functionality
- REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life
- Flexible battery system: works with all MILWAUKEE® M12™ batteries



REDLITHIUM™

Display size (Inch)	4.3
Display resolution (pixels)	480×272
Camera head diameter (mm)	10
Camera cable length (mm)	1200
Kit included	No batteries supplied, No charger supplied, Kitbox
Weight with battery pack (EPTA) (kg)	0.88 (M12 B2)
Article Number	4933480739