



Great fingertip sensitivity, palm dipped. For fine assembly work in dry environments.

■ TEGERA® INFINITY 8807T



[Learn more](#)

CUT D GLOVE WITH TOUCHSCREEN FUNCTIONALITY

Dexterous, thin glove with cut resistant level D, suitable for fine assembly work. 15 gg knitted with CRF® cut resistant technology. Palm dipped with super soft nitrile foam that provides excellent grip on dry surfaces. Reinforced thumb crotch for improved longevity. Breathable materials for all day comfort. Protection against contact heat up to 100°C/212°F. Touchscreen functionality.

CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Extra comfortable

FUNCTIONS

- Withstands contact heat up to 100°C
- For touchscreen
- Reinforcement between index finger and thumb
- Thin



PREVENTS RISK OF

Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE

Fine assembly, Assembly, Machine operating, Building and construction, Carpentry, Installation work, HVAC installation, Sheet-metal work, Engineering, Transport work, Machine driving, Warehouse work, Airport work, Metalwork, Glass industry work, Repair work, Paper industry work, Service work, Shop work

PRIMARY INDUSTRIES OF USE

Pulp and paper, Glass, bricks, concrete, Metal fabrication, Machinery and equipment, MRO, Automotive, Transportation, Utilities, Building and construction, Logistics, Facilities, Service, Retail

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves

CATEGORY Cat. II

COLLECTION Infinity

KNITTING GAUGE (GG) 15

LINING MATERIAL CRF® Technology, Glass fibre thread, HPPE, Nylon, Spandex

LENGTH 205-270 mm

DEXTERITY 5

GRIP DESIGN Foam grip pattern

COLOUR Black

PAIRS PER: BUNDLE/CARTON 6/120

DISPLAY TYPE Bulk pack

DIPPING Palm-dipped

DIPPING MATERIAL Nitrile foam, Waterbased PU

CUFF STYLE Knitwrist cuff

CUFF MATERIAL Textile

CUT RESISTANCE (EN ISO 13997) Cut resistance level D

CUT RESISTANCE (EN ISO 13997) TDM: 16.4 N

INNER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Nylon, Glass fibre thread, Elastane

OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE



TP TC 019:2011



EN ISO 21420:2020



EN 388:2016+A1:2018 4X43D



EN 407:2020 (No flame protection) X1XXXX



Contact heat rating valid for palm area only

FEATURES



For touchscreen



Cut protection

SIZE		ARTICLE NUMBER	EAN
10	XL	8807T-10	7333506018037
11	XXL	8807T-11	7333506018181
5	XXS	8807T-5	7333506017283
6	XS	8807T-6	7333506017436
7	S	8807T-7	7333506017580
8	M	8807T-8	7333506017733
9	L	8807T-9	7333506017887

ejendals

Limavägen 28, SE-793 32 Leksand, Sweden

Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com