

Ultrasonic Cleaning Tanks

FEATURES

- Removes Dirt, Grease, Corrosion
- For best results use appropriate cleaning fluid or solvent suitable for the item
- All XL tanks have an operating frequency of 28kHz as standard and require a 3 Phase supply
- Tank and Housing Made from Stainless Steel
- Wire Basket Supplied - at no additional charge
- Separate Ultrasonic Power Generator Supplied - with digital controls and clear LED display
- Constructed from 2mm thick SUS304 stainless steel for maximum durability
- Remote feature on generator to allow start and stop of ultrasonic generator via a remote socket, (Additional switch or PLC controller required, not included)

RS PRO Industrial 145 Litre Ultrasonic Cleaner Tank with 6000W Heater

RS Stock No.: 2135183



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Ultrasonic Cleaning Tanks

Product Description

2160W Industrial 145L Ultrasonic Cleaner Tank with 6000W Heated Bath - Ideal for industrial large-scale cleaning

Key Specifications

Frequency: 28KHz

Internal Tank Dimension: 700 (L) x 500 (W) x 445 (H) mm

Tank Capacity: 145L

Drain tap has a standard 1" BSP pipe thread

General Specifications

Supplied with Stainless Steel Basket and Lid
 Model Range: 145L
 Controls: Dial / Digital
 Basket: Included
 External Tank Dimensions: 900 (L) x 700 (W) x 770 (H) mm
 Internal Tank Dimension: 700 (L) x 500 (W) x 445 (H) mm
 Basket Size: 680 (L) x 480 (W) x 310 (H) mm
 Ultrasonic Freq (KHz): 28
 91db noise level at 1m distance without lid (Ear protection recommended)

Mechanical Specifications

2mm Grade 304 Stainless Steel

Electrical Specifications

Generator supplied with 3 pin 230v plug
 Heating supplied via 3 phase 16 amp 5 pin plug, neutral required
 RCD protection is advised
 2160 Ultrasonic Power
 6000W Heating

Ultrasonic Cleaning Tanks

Protection Category

Ultrasonic Cleaners	1945907 1L CLEANING SOLUTION - ENGINE 1945911 1L CLEANING SOLUTION - GLASS/OPT 1945908 1L CLEANING SOLUTION - OXIDATION 1945909 1L CLEANING SOLUTION - SENSITIVE
---------------------	---

Additional Information

EAN	
Custom Tariff Number	8456200000

Classification

eCl@ss (Version)	
UNSPSC (Version)	

Approvals

Declarations	MFR Declaration of Conformity
Hazardous Area Certification	ATEX / IECEx
Standards Met	VDE

Similar Products

Stock No.	Brand	Product Name
2135190	RS PRO	57 Litre Ultrasonic Cleaner Tank
2135193	RS PRO	90 Litre Ultrasonic Cleaner Tank
2135195	RS PRO	99 Litre Ultrasonic Cleaner Tank
2135179	RS PRO	112 Litre Ultrasonic Cleaner Tank
2135181	RS PRO	144 Litre Ultrasonic Cleaner Tank
2135183	RS PRO	145 Litre Ultrasonic Cleaner Tank
2135185	RS PRO	206 Litre Ultrasonic Cleaner Tank
2135188	RS PRO	288 Litre Ultrasonic Cleaner Tank