

2m (6.6ft) VESA Certified DisplayPort Cable - 10 Pack - DisplayPort 1.2 Cord with Latches, 4K 60Hz UHD, DP to DP Cable for Monitor, Latching DP Connectors

Product ID: DISPL2M10PK



Facilitate multi-monitor setups using this DisplayPort 1.2 Cable 10-Pack. This cable facilitates high bandwidth video and multi-channel audio and is ideal for 4K workstations, docks, and high performance GPUs. Connect a 4K 60Hz UHD DisplayPort monitor to a host computer or MST hub.

For seamless operation between DisplayPort-enabled devices, the DisplayPort 1.2 Cable is VESA Certified for guaranteed DP 1.2 and backward compatibility with DP 1.1.

This DisplayPort cable features a flexible TPE outer jacket and can be routed around corners and desk edges. Robust strain reliefs enable convenient positioning of the cable, and latching gold-plated DP connectors attach securely to prevent accidental disconnection.

The Certified DisplayPort Cable supports the following DP 1.2 features:

- Resolutions up to 4K 60Hz, using a compatible DP source and display
- Supports high refresh rates including 1080p 120Hz and 1440p 75Hz
- High-Bandwidth Digital Content Protection (HDCP) for a secure connection between source and display
- Multi-Stream Transport (MST) for daisy-chaining multiple monitors
- 8 Uncompressed Digital Audio Channels
- Backward compatible with DP 1.1

This DP 1.2 Cable is constructed with braided aluminum mylar shielding to minimize EMI for clear, consistent audio/video output and long-term reliable performance.

Certifications, Reports and Compatibility



Applications

Features

- **PRACTICAL 10 PACK:** These VESA Certified DisplayPort 1.2 cables come in a practical 10-pack to facilitate larger deployments and multi-monitor workstation setups; Supports 4K 60Hz video with HBR2, 8Ch Audio, Multi-Stream Transport (MST), and 3D stereo audio
- **QUALITY CONSTRUCTION:** 28AWG wire with gold-plated connectors for improved signal integrity and reliability; Al-Mylar foil with copper braid for enhanced EMI protection; Backward compatible with DP 1.1
- **APPLICATIONS:** Convenient 10-pack is ideal for offices/boardroom/conference room/classroom setups and professional multi-display installations w/high-performance GPUs; Use with 4K UHD or 1080p docking stations/monitors/projectors/video walls
- **RELIABLE DESIGN:** Durable ABS connectors with flexible TPE strain reliefs & jacket prevents fraying/damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection
- **SPECS:** 2-meter (6.6-foot) Cable; 10 Pack; Black; DisplayPort v1.2; 4K 60Hz w/HBR2/MST/GTC; DP Latching Male to Male; 28AWG; 0.29in (7.3mm) O.D.; TPE Jacket; ABS Connector Shell; Al-Mylar Foil/Braided Shield; Single SKU available (DISPL2M)

Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

Performance

Video Revision	DisplayPort 1.2
Maximum Data Transfer Rate	21.6 Gbps

Audio Specifications DisplayPort - 7.1 Channel Audio

Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - DisplayPort (20 pin)

Environmental

Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Humidity	10% to 85 % RH

Physical Characteristics

Color	Black
Connector Style	Latching
Wire Gauge	28 AWG
Material	ABS
Cable Length	6.6 ft [2 m]
Cable OD	0.3 in [7.3 mm]
Product Length	6.6 ft [2.0 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.5 in [1.2 cm]
Weight of Product	4.7 oz [134.0 g]

Packaging Information

Package Length	18.1 in [46.0 cm]
Package Width	13.8 in [35.0 cm]
Package Height	3.9 in [10.0 cm]
Shipping (Package) Weight	3.0 lb [1.4 kg]

What's in the Box

Included in Package 10 - 2m DisplayPort Cable

**Warranty
Information**

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*