

GRINDER DUO 125/230 MM

- Powerful motor protected against abrasive particles for longer life
- Two-position side handle for better comfort of use
- Shaft lock for quick and easy disc changes
- Specific opening for quick replacement of the brushes



Grinder 2200W 230 mm DWE494

No-load speed 6600 rpm

+ Grinder 900W 125 mm DWE4157

No-load speed 11800 rpm

with protective guard, 2-position side handle, indoor/outdoor flange, service key, case

DWE494TWIN-QS

5 035 048 665 879