

# 18V Drill Driver Brushless LXT

## DDF490

65 Nm, 0 – 1 900 min<sup>-1</sup>

Model DDF490 is a Drill Driver powered by an 18V LXT Li-ion battery

This model ensures sufficient torque by adopting a Brushless Motor is lightweight and compact, easy to handle even in narrow spaces. Features and Benefits: Max.torque of 65Nm, Mechanical 2 speed, Electric brake, Variable speed control by trigger.



### Technical specifications

|                                                       |                                      |
|-------------------------------------------------------|--------------------------------------|
| Nominal Battery Voltage                               | 18 V                                 |
| Voltage LXT                                           | ✓                                    |
| Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)            | Li-ion                               |
| Brushless Motor                                       | ✓                                    |
| No load speed                                         | 0 - 500 / 0 - 1900 min <sup>-1</sup> |
| Max. fastening torque Hard/Soft                       | 50 / 27 Nm                           |
| Max Torque                                            | 65 Nm                                |
| Torque setting                                        | 20                                   |
| Max. Drilling Diameter in Wood                        | 38 mm                                |
| Max. Drilling Diameter in Steel                       | 13 mm                                |
| Driving Shank                                         | 1/2"-20UNF "                         |
| Drill Chuck Capacity                                  | 1,5 - 13 mm                          |
| Drilling Capacity Wood (Self-feed bit)                | 38 mm                                |
| Vibration Level, Drilling into metal                  | ≤ 2,5 m/s <sup>2</sup>               |
| Vibration Uncertainty (K Factor), Drilling into metal | 1,5 m/s <sup>2</sup>                 |
| Sound Pressure Level (L <sub>pA</sub> )               | 78 dB(A)                             |

### User benefits

- Keyless chuck for easy bit installation and removal
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Reversing switch is conveniently located
- Electric brake for maximum productivity and increased operator safety
- Built-in LED light with pre-glow and afterglow functions illuminates the work area
- Battery protection system automatically shuts off power when the battery level is low

Link to product - [www.makitauk.com](http://www.makitauk.com)



# Related products

## Other

User manual

Parts drawing