

## FEATURES

- **Level VI Efficiency**
- **Universal Input**  
90~264V-AC  
47~63Hz
- **Short Circuit Protected**
- **Operating Temperature** 0~40°C
- **Limited Power Source (LPS)**

## RS PRO 24V dc Power Supply, 0 → 1.25A, 3-Pin IEC Connector

RS Stock No.: 144-0972



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*Please provide an introduction to the product with relevant details stating:*

- *What are the products used for*
- *Applications they are most suited for or not suited for*
- *What are they used with etc*

## General Specifications

Input Connector	IEC C14
Input Plug Type	3-Pin IEC
Output Connection Type	2.1 x 5.5 mm Connector
Number of Outputs	1
Energy Efficiency Level	VI
Cable Length	1830mm

## Electrical Specifications

Input Specifications	
Rated Input Voltage	100 to 240V ac
Efficiency	87%

Output Specification	
Hold Up Time (Typ.)	10ms minimum

## Mechanical Specifications

Overall Dimensions	99mm x 52mm x 36mm
Overall Length	99mm
Overall Depth	36mm
Overall Width	52mm

## Operation Environment Specifications

Storage Temperature Range	0°C to 40°C
---------------------------	-------------

## Approvals

### Safety Standard

AS/NZS 60950.1, BS EN 60950-1, CB, CE, CSA  
C22.2 No.60950-1-07, CUL, EN 60950-1, FCC,  
J60950-1, SAA, TUV, UL, UL 60950-1

