

Reciprocating Saw LXT®

DJR360

18V X2 • 0 – 3 000 min⁻¹ • 32 mm

Extremely efficient brushless reciprocating saw

An efficient brushless saw for spark-free cutting of metal and demolition work. Two 18V LXT® batteries achieve a voltage of 36V. Two speeds, stroke length of 32 mm and stroke rate of 0 – 2 800 min⁻¹ with continuous control from the switch. Quick-release blade attachment.



Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Brushless Motor	✓
Strokes per Minute (SPM)	0 - 2300 / 3000 min ⁻¹
Length of Stroke	32 mm
Max. Cutting Capacity in Wood (90°)	255 mm
Max. Cutting Capacity in Steel Pipe	130 mm
Sound Power Level (L _{WA})	96 dB(A)
Sound Pressure Level (L _{pA})	88 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	4,0 - 4,7 kg
Product Dimensions (L x W x H):	449 x 116 x 243 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Vibration Level, Cutting Boards	16,5 m/s ²

User benefits

- Tool-less blade change and shoe adjustment
- LED light illuminates the work site
- Wide hanging hook, e.g. for scaffolding
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing