

**EK EKPE 130 G**



Sample photo

**Order symbol:** EKPE 130 G  
**Product nbr:** 2538043  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074013583  
**EI. number:**  
 Finland: 3425421  
 Electric No. Italy: 7501045  
 Electric No. Sweden: 2538043

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

| Dimensions: | Length | Width | Height | Accessories:   |
|-------------|--------|-------|--------|----------------|
| mm:         | 380    | 280   | 130    | EKPG Base, PC  |
| inch:       | 15.0   | 11.0  | 5.1    | EKP 30-G Cover |

**Materials:**

**Material:** Polycarbonate

**Base colour:** RAL 7035 -light grey

**Cover screws material:** Polyamide

**Cover colour:** RAL 7035 -light grey

**Cover screws colour:** Grey

**Gasket material:** Polyurethane

**Accessories:**

EKP 80-G Cover

EKP 30-T Cover

EKP 80-T Cover

EKPVT Mounting plate

EKPXT Mounting plate isolated

EKV 22 DIN-35 Mounting rail

EKV 32 DIN-35 Mounting rail

EKPZR Extension frame

**Temperatures:**

**Temperature °C (short term):** -40 ... 120 °C

**Temperature °C (continuous):** -40 ... 80 °C

**Temperature °F (short term):** -40 ... 250 °F

**Temperature °F (continuous):** -40 ... 175 °F

**Rating:**

Ingress Protection (EN 60529): IP66/IP67

Impact Resistance (EN 62262): IK08

Electrical insulation: Totally insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: UL 508

Flammability Rating: UL 746C 5"

Glow Wire Test (IEC 695-2-1) °C: 960

NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

**Accessories:**

EKPE Base, PC

**Certificates:**

SGS Fimko

Gost R

