

Datasheet

RS POF Simplex Fibre Optic Connector, 1.5dB Insertion Loss

RS Stock 178-1328



Specifications

- Low cost fiber optic components
- Guaranteed link performance over temperature
- High speed links: dc to 5 MBd
- Extended Distance Links: 6 mA peak Supply Current
- Low Cost Standard Link: dc to 1 MBd
- Photo Interrupter Link
- Compact, low profile
- Horizontal and vertical mounting
- N-Plex stackable
- Flame retardant
- Easy to use receivers
- Simplex, duplex and latching connectors, flame retardant material
- Easy connecting
- Simplex, duplex and latching connectors flame retardant material
- Low loss plastic cable
- Selected super low loss simplex, simplex and zip cord style duplex, flame retardant
- No optical design required
- Auto – insert able and wave solderable