





LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE DWN APVD
J	—	F	REVISED	ECR-08-005781	05MAR'08 J.S S.M
		F1	REVISED PER ECO-10-000444		01FEB10 KK HMR

- 注:
- 適用製品規格 108-5302
 - 5極ハウジングの回路NO.2と4のコンタクト2本抜き仕様
 - かん合相手製品型番
3.96MM ピッチ 2極プラグハウジング: 表2参照
リセコンタクト: 175151-X (AWG#26-#22)
: 175152-X (AWG#20-#16)
- △ C寸法は基板穴をパンチ加工する場合、
基板にクラックが発生しない様、寸法設定してください。
- △ 4極ハウジングの回路NO.1と3のコンタクト2本抜き仕様
- △ 4極ハウジングの回路NO.2と4のコンタクト2本抜き仕様


- NOTES:
- PRODUCT SPEC 108-5302
 - CIRCUIT NO.2 AND 4 ARE VACANT OF 5POS HOUSING
 - MATING CONN. P/N
3.96MM PITCH 2POS PLUG HSG: SEE TABLE 2
REC CONTACT: 175151-X (AWG#26-#22)
: 175152-X (AWG#20-#16)
- △ PLEASE DECIDE THE DIMENSION C SO THAT PREVENT CRACKING OF P.C.B
- △ CIRCUIT NO.1 AND 3 ARE VACANT OF 4POS HOUSING
- △ CIRCUIT NO.2 AND 4 ARE VACANT OF 4POS HOUSING
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



178498のみ対象
(APPLIED P/N 178498 ONLY)



断面 "A"- "A"
(SECT)



型番 178498 対象 (APPLIED P/N 178498) 型番 178497 対象 (APPLIED P/N 178497)
178499 対象 (APPLIED P/N 178499)

表1
TABLE1

NO.	名称 (NAME)	材料 (MATERIAL)
①	タブ (TAB)	黄銅 鍍めつき (BRASS TIN PLATED)
②	ヘッダーハウジング (HEADER HOUSING)	6/6ナイロンガラス強化 (6/6 NYLON GLASS FILLED)

表 2 (TABLE 2)

ヘッダーアセンブリ P/N (HDR ASS'Y P/N)	極数 (POS.)	適合相手 P/N (MATING CONN. P/N)
178497	4	178481
178498	5	178482
178499	6	178483

基板レイアウト寸法 (P.C.B LAYOUT)
適用基板厚 1.6 (APPLICABLE P.C.B THK 1.6)

SUPERSEDED BY 178497-1			3.96MMピッチ 4極 (3.96MM PITCH 4POS)	自然色 (NATURAL)	0-178497-1
△	11.88	16.98		青 (BLUE)	5-178497-6
△	11.88	13.58	7.92MMピッチ 2極 (7.92MM PITCH 2POS)	赤 (RED)	6-178497-2
△	11.88	16.98		自然色 (NATURAL)	5-178497-1
OBSOLETE △	19.80	21.50	3.96MMピッチ 6極 (3.96MM PITCH 6POS)	黒 (BLACK)	178499-9
				青 (BLUE)	178499-6
				黄色 (YELLOW)	178499-4
				赤 (RED)	178499-2
OBSOLETE △	15.84	17.54	7.92MMピッチ 3極 (7.92MM PITCH 3POS)	自然色 (NATURAL)	178498-1
				黒 (BLACK)	3-178498-9
				青 (BLUE)	3-178498-6
				黄色 (YELLOW)	3-178498-4
OBSOLETE △	15.84	17.54	3.96MMピッチ 5極 (3.96MM PITCH 5POS)	赤 (RED)	3-178498-2
				自然色 (NATURAL)	3-178498-1
				黒 (BLACK)	178498-9
				青 (BLUE)	178498-6
	15.84	17.54	3.96MMピッチ 4極 (3.96MM PITCH 4POS)	黄色 (YELLOW)	178498-4
				赤 (RED)	178498-2
	11.88	13.58		自然色 (NATURAL)	178498-1
	"N"	"M"		黒 (BLACK)	178497-9
	"L"			青 (BLUE)	178497-6
				黄色 (YELLOW)	178497-4
				赤 (RED)	178497-2
	11.88	13.58		自然色 (NATURAL)	178497-1
寸法 (DIMENSION)	"N"	"M"	コネクタピッチ及び極数 CONN.PITCH AND POS	ハウジング色調 (COLOR)	型番 (P/N)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Y.NARISAWA 08MAR'91	Tyco Electronics Corporation Kawasaki, Japan	
DIMENSIONS: 単位: 純 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	CHK N.ONQUE 13MAR'91	NAME 名称 AMP UP CONN. 3.96MM PITCH 4-6POS TAB HEADER ASSY (H TYPE)	
10以下 ± 0.2	10を超え30以下 ± 0.25	APVD Y.FUJITA 13MAR'91	SIZE CAGE CODE DRAWING NO A2 00779 C-178497	
30を超え100以下 ± 0.3	ANGLES ± 3°	PRODUCT SPEC 製品規格	RESTRICTED TO	
MATERIAL 材料	FINISH 仕上	APPLICATION SPEC 取付適用規格	—	
SEE TABLE 1	SEE TABLE 1	WEIGHT	—	
CUSTOMER DRAWING			SCALE 尺度 SHEET 1 OF 1 REV F1	