

Datasheet

RS Pro Line Mounting Hydraulic Flow Control Valve, G 1/4, 400 bar

RS Stock No: **390-7673**



Product Details

RS Pro line mounting hydraulic flow control valve offers connection through G 1/4 ports and withstands pressure up to 400 bar. This double-acting valve allows flow in both the directions. The needle adjustment provides accurate control over the flow rate.

Features and Benefits

- Needle adjustment for full shut off or accurate control for a wide range of flow rates
- A graduated adjustable scale below the handle to indicate valve position
- Locking screw prevents movement accidental or due to vibration
- Nitrile rubber seals

**Specifications:**

Body Material	Carbon Steel
Connection Port Thread	1/4 in G
Seal Material	Nitrile Rubber
Thread Standard	G
Maximum Flow Rate	25 L/min
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-20°C
Maximum Operating Pressure	400 bar
Thread Size	1/4 in