

Eaton 248256

Catalog Number: 248256

Eaton Distribution parts. Release relay, 250VAC, 1 N/C, 3-8A, 1HP

General specifications



Product Name	Catalog Number
Eaton Distribution parts	248256
EAN	Product Length/Depth
4015082482565	80 mm
Product Height	Product Width
70 mm	17.5 mm
Product Weight	Compliances
0.104 kg	RoHS conform

Product specifications

Mounting method

DIN rail

Current rating of control contacts

1 A

Just-operate current - max

8 A

Just-operate current - min

3 A

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

1

Number of contacts (normally open contacts)

0

Number of electrical switching cycles per hour - max

3600

Rated operational voltage (U_e) - max

250 V

Rated uninterrupted current (I_u)

10 A

Rated uninterrupted current (I_u) - max

8 A

Rated uninterrupted current (I_u) - min

3 A

Switching power of control contacts - max

7.7 VA

Switching voltage of control contacts - max

250 V

Switch-off time delay - max

0 ms

Width in number of modular spacings

1

Built-in depth

60 mm

Degree of protection

Resources

Declarations of conformity

[DA-DC-03_Z-LAR](#)

Drawings

[eaton-dimensions-mas-lar.jpg](#)

[eaton-wiring-diagram-lar-o.jpg](#)

Installation instructions

[IL019154ZU](#)

IP20

Lifespan, electrical

100000 c (contacts)

Lifespan, mechanical (control contacts)

0 c (contacts)

Voltage type

AC



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia