



Fuse-link, LV, 32 A, AC 500 V, BS88/A2, 22 x 85 mm, gM, BS, 32M35

Catalog No. AA032M35

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	32
Motor current rating	I	A	32M35
Rated voltage			AC 500 V
Construction size			BS88/A2
Size			22 x 85 mm
Utilization category			gM
Description			motor-rated
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-2 IEC 60269-2
Optional accessories			fuse-holder CM32F and RS32

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)

Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])

Construction size			Other
Rated current		A	32
Rated voltage		V	500
Voltage type			AC
Rated switching capacity		kA	80
Utilization category			Other
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

### Additional product information (links)

Product datasheet (pdf)	<a href="http://www1.cooperbusssmann.com/pdf/088d47f0-ca3b-48f8-9711-fb2f26d234fe.pdf">http://www1.cooperbusssmann.com/pdf/088d47f0-ca3b-48f8-9711-fb2f26d234fe.pdf</a>
-------------------------	---