

METAL QUICK-ACTING COUPLERS

✉ Email 🖨 Print

Parker Legris offers a range of metal couplers compatible with a large selection of fluids. Simple to install, with or without shut-off valves, these couplers offer a high flow rate capability.

PART NUMBER:

3150 00 61

BODY MATERIAL:

NICKEL PLATED BRASS

GRIPPING RING:

STAINLESS STEEL

O-RING MATERIAL:

NBR

DIAMETER NOMINAL (DN):

3

CONNECTION 1 THREAD SIZE (METRIC):

na

CONNECTION 1 THREAD STYLE:

na

CONNECTION 2 TUBE O.D. (MM):

4

CONNECTION 3 TUBE O.D. (MM):

na

COLOR:

na

PRODUCT TYPE:

Metal Quick Acting Coupler

[Reset Attributes](#)

WHERE TO BUY

PRODUCT OVERVIEW	-
TECH SPECIFICATIONS	+

Print Tech Specifications

PERFORMANCE CHARACTERISTICS

HANDLE

na

MAXIMUM PRESSURE (BARG)

20

MINIMUM WORKING TEMPERATURE (°C)

-20

MAXIMUM WORKING TEMPERATURE (C)

100

BOX QUANTITY

10

WEIGHT (KG)

0.008

APPLICATION

Workshops, Flushing, Spraying, Packaging, Factory Automation, Filling Systems, Cleaning

MEDIA

Compressed air, water

Print Tech Specifications

PRODUCT SUPPORT	+
------------------------	---

RECOMMENDED



Polyamide (PA) Recoil Tubing



Blowgun Kits



Braided Polyurethane (PU) Recoil Hose



CONTACT US

Parker Hannifin Manufacturing France SAS

Fluid System Connectors Division Europe
Parc Alcyone - Bat. D
1 rue André et Yvonne Meynier - CS 46911
35069 Rennes Cedex France

Phone

Phone: +33 (0) 2-99-25-55-00



EMAIL PARKER

Parker Hannifin +

Products

About Parker

Investors

Community

Careers

Global Operations +

Divisions

Sales Companies

Worldwide Locations

Distribution Network

ParkerStore™ Network

Company Information +

Newsroom

Event Calendar

Working with Parker

Product Brands

History